



String Lights

Make your home vibrant with a range of colours that you can adjust to make special moments even more memorable. Use with your existing Wi-Fi to control with the WiZ app or your voice.

PRODUCT HIGHLIGHTS

- Full colour
- Low Voltage
- Outdoor-rated




Instant setup for all your smart home functionalities

Access all smart features instantly, simply by connecting your new lights to your existing Wi-Fi. You can control lights when you're away from home and set schedules to turn them on and off automatically. All without needing to install additional hardware. Keep the controller within Wi-Fi range, and all linked lights will be fully controllable even out of Wi-Fi range.



Control with any Matter smart home platform

This product is Matter-certified, allowing easy control through Google Home, Amazon Alexa, Apple Home or any other Matter-based smart home platform of your choice.



Always feel safe and secure with automated outdoor lights

Schedule your outdoor lights to turn on every day before you get home, so that you can clearly see your environment and feel safe. Set your lights to turn off automatically in the morning, or when they are not necessary, and save energy.



Create your perfect light scene

Make your own mix of different colour and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



Beautify your garden with millions of colours and dynamic modes

Choose from millions of light colours, from energising cool white to soft warm white, and create the best ambience for your outdoor activities. Or simply apply a preset dynamic light mode like Ocean, Forest or Party to create an amazing atmosphere and lift the mood.



Low-voltage technology and easy installation

Designed for outdoor enjoyment! No complicated wiring or special installation required – just plug it in and go. If you want to change the light's location, just unscrew the adapter and move it somewhere else.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Outdoor
Lamp shape: Rectangle
Dimmable: Yes

DESIGN AND FINISHING

Colour: White
Material: Plastic

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 15,000

EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: Yes
LED integrated: Yes
LED lamp(s) included: Yes
On/off switch on wire: Yes
Power adapter included: Yes
Remote control included: No

LIGHT CHARACTERISTICS

Colour consistency: 7 SDCM
Colour rendering index (CRI): ≥ 80
Colour temperature: 2700-5000 K
Warm-up time to 60% light: 2
Luminous efficacy (rated) (nom.): 10 lm/W

MISCELLANEOUS

Especially designed for: Garden
Balcony

OTHER CHARACTERISTICS

Lamp current: 200 mA

POWER CONSUMPTION

Power factor: 0.5
Voltage: 220-240 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 2.15 kg
Overall height: 200 mm
Overall length: 14,800 mm
Overall width: 45 mm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Lumen output bulb included: 10
Total lumen output fixture: 120
Light colour: 2700-5000 (RGB)
Wattage bulb included: 12
Maximum wattage replacement bulb: 12
IP code: IP65 | Dust-tight and jet-proof
Class of protection: Class II – Double Insulated
Light source replaceable: Yes
Number of light sources: 12

WHAT'S SUPPORTED

Compatible with Effects feature: Yes
WiFi: Wireless G
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth
WiFi (2.4GHz)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8719514554474
Net weight: 2.14 kg
Gross weight: 2.54 kg
Height: 33 cm
Length: 12.7 cm
Width: 39.4 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.