



Bulb 100W A60 B22



Jazz up your home with this WiZ full-colour smart bulb. Easily adjust the brightness, switch between cool and warm white light, and select from literally millions of colours to personalise your lighting experience. Plus, you can control it using the WiZ app or your voice, so you don't need any extra hardware

PRODUCT HIGHLIGHTS

- Full colour smart bulb
- Up to 1521 @ 2700K lumens
- Easy plug and play
- Control with app or voice



Control with any Matter smart home platform

This product is Matter-certified, allowing easy control through Google Home, Amazon Alexa, Apple Home or any other Matter-based smart home platform of your choice.



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Millions of colours and changing light modes to make your day

Choose any light colour you like or simply apply a dynamic light mode that we've designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energising cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



Dim your smart lights even without a dimmer

Simply adjust lights to your desired brightness level using your smartphone, the WIZ control accessory or just your voice. No need to install an expensive dimmer!



Control your smart lights from anywhere

No need to worry if lights were left on while no one's at home. Simply turn them off from wherever you are, with your smartphone.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: A60
Socket: B22
Technology: Smart Wi-Fi
Type of glass: Frosted
Dimmable: Yes

LAMP DIMENSIONS

Height: 12 cm
Weight: 0.062 kg
Width: 6 cm

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 15,000

LIGHT CHARACTERISTICS

Colour consistency: 6 SDCM
Colour rendering index (CRI): 80
Colour temperature: 2200-6500 K
Light Colour Category: Full colour
Starting time: <0.5 s
Warm-up time to 60% light: Instant full light
Luminous efficacy (rated) (nom.): 121.68 lm/W

OTHER CHARACTERISTICS

Lamp current: 70 mA

PACKAGING INFORMATION

EAN: 8719514865891
EOC: 871951486589100
Product title: Wi-Fi BLE 100W A60 B22
822-65 RGB 1PF/6

POWER CONSUMPTION

Power factor: 0.5
Voltage: AC 220-240 V
Wattage: 12.5 W
Energy efficiency label (EEL): E
Energy consumption kWh/1,000 hours: 13

PRODUCT DIMENSIONS AND WEIGHT

Length: 12 cm

RATED VALUES

Rated lifetime: 15,000
Rated power: 12.5 W

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Frequency: 50-60
EPREL Registration Number: 2224718
Flux measurement reference: Sphere

WHAT'S SUPPORTED

Compatible with Effects feature: Yes
WiFi: Wireless G
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth WiFi (2.4GHz)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8719514865891
Net weight: 0.06 kg
Gross weight: 0.11 kg
Height: 16 cm
Length: 7 cm
Width: 7 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.