

## Panel Ceiling 36 W Rectangular

This sleek rectangular panel light can be adjusted for warm and cool lighting options. Easy to install, dimmable and blends well into modern design aesthetics too.

## PRODUCT HIGHLIGHTS

- Tunabel white
- Dimensions: 1,195\*295 mm
- IP20/Plastic/Black



### Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!




### Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



### Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



### Create your perfect light scene

Make your own mix of different colour and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



### Set the right ambience with tunable warm to cool white light

Choose from a wide range of energising cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



### Dim your smart lights even without a dimmer

Simply adjust lights to your desired brightness level using your smartphone, the WiZ control accessory or just your voice. No need to install an expensive dimmer!



# SPECIFICATIONS

## BULB CHARACTERISTICS

Intended use: Indoor  
Dimmable: Yes

## DESIGN AND FINISHING

Colour: Black  
Material: Metal Plastic

## DURABILITY

Average life (at 2.7 hrs/day): 20 year(s)  
Lumen maintenance factor: 70%  
Number of switch cycles: 20,000  
Nominal lifetime: 20,000

## EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: Yes  
LED integrated: Yes  
Remote control included: No

## LIGHT CHARACTERISTICS

Colour rendering index (CRI):  $\geq 80$   
Colour temperature: 2700-6500 K  
Warm-up time to 60% light: 2  
Luminous efficacy (rated) (nom.): 94 lm/W

## MISCELLANEOUS

Especially designed for: Living Room  
Dining Room Bedroom Children's room

## OTHER CHARACTERISTICS

Lamp current: 190 mA

## POWER CONSUMPTION

Power factor: 0.9  
Voltage: 220-240 V

## PRODUCT DIMENSIONS AND WEIGHT

Net weight: 2.65 kg  
Overall height: 40 mm  
Overall length: 1,195 mm  
Overall width: 295 mm

## SERVICE

Warranty: 2 year(s)

## TECHNICAL SPECIFICATIONS

Total lumen output fixture: 3400  
Light colour: 2700-6500  
Wattage bulb included: 36  
IP code: IP20 | Finger-protected  
Class of protection: Class II – Double Insulated

## WHAT'S SUPPORTED

Compatible with Effects feature: Yes  
WiFi: Wireless G  
Defined support period: Minimum of 60 months after introduction date  
Max. number of accessories: 9999  
Communication protocol: Bluetooth WiFi (2.4GHz)

## PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8720169071414  
Net weight: 2.64 kg  
Gross weight: 3.35 kg  
Height: 31.7 cm  
Length: 6 cm  
Width: 121.1 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.