



## Outdoor wall light with camera

What's going on out there? Never be in the dark with the WiZ smart outdoor wall light with integrated security camera. Our weatherproof camera's light comes on whenever motion is detected – surprising potential intruders or helping you enter your home comfortably after nightfall.

## PRODUCT HIGHLIGHTS

- Built-in camera
- Outdoor-rated
- Full colour




### Beautify your garden with millions of colours and dynamic modes

Choose from millions of light colours, from energising cool white to soft warm white, and create the best ambience for your outdoor activities. Or simply apply a preset dynamic light mode like Ocean, Forest or Party to create an amazing atmosphere and lift the mood.



### Stay informed at any time when motion or sound is detected

The WiZ outdoor camera automatically notifies you when motion or sound is detected outside your home. Enjoy peace of mind even when you're away!



### Observe activities outside your home

Monitor your home's outdoor areas, in real time and from anywhere, with the WiZ outdoor camera's live video streaming feature. Stay worry-free when you're away by reviewing automated incident notifications, observing the live video stream and preventing false alarms.



### Turn on lights automatically when motion is detected

The WiZ outdoor camera light turns on automatically when motion is detected, so you can see your way in at night and keep potential intruders out.



### Built-in speaker and mic

Communicate directly with anyone near the camera while live-streaming. The built-in speaker and microphone enables an easy, remote conversation with your family. Or use it to warn any unwanted visitors.



### Optimal outdoor performance (IP44)

This WiZ outdoor light has been rigorously tested to ensure its suitability for outdoor use. It's specifically designed to endure weather conditions ranging from intense sunlight to heavy downpours.



# SPECIFICATIONS

## DESIGN AND FINISHING

Colour: Black  
Material: Metal

## DURABILITY

Nominal lifetime: 25,000

## EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: Yes  
LED integrated: Yes  
LED lamp(s) included: Yes  
Remote control included: No

## LIGHT CHARACTERISTICS

Colour rendering index (CRI):  $\geq 80$   
Colour temperature: 2700 K  
Luminous Flux: 1,250 lm

## MISCELLANEOUS

Especially designed for: Garden  
Balcony  
Space sense: Yes

## POWER CONSUMPTION

Voltage: 5 V

## PRODUCT DIMENSIONS AND WEIGHT

Net weight: 1.5 kg  
Cable length: 240  
Recessed distance: 2,000 mm  
Overall height: 375 mm  
Overall length: 167 mm  
Overall width: 115 mm

## SERVICE

Warranty: 2 year(s)

## TECHNICAL SPECIFICATIONS

Light colour: 2700  
Energy class included light source: E  
Wattage bulb included: 10.5  
Class of protection: Class I – Earthed  
Light source replaceable: No  
Dimmable: Wireless Dim – Do not use with a dimmer  
Number of light sources: 1  
Image sensor camera: No  
Camera lens field of view (degrees): 120  
Camera digital Zoom: No

## THE CAMERA

Max. video resolution: 1080P  
Video modes: 1080P  
Video features: 30FPS  
Motion detection: Motion, people and sound detection  
Night Vision: Yes, with infrared LED  
Weatherproof: Yes  
Microphone: Yes  
Audio: Two-way audio  
Operating temperature: -20°C to 45°C  
Connectivity protocol: WiFi (2.4GHz)  
Sound alarm: No  
Two-way talk: Yes  
Storage way: Local & Cloud storage (subscription)

## WHAT'S SUPPORTED

Compatible with Effects feature: Yes  
WiFi: Wireless G  
Defined support period: Minimum of 60 months after introduction date  
Max. number of accessories: 9999  
Communication protocol: Bluetooth  
WiFi (2.4GHz)

## PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8720169072114  
Net weight: 1.47 kg  
Gross weight: 1.98 kg  
Height: 44.5 cm  
Length: 23 cm  
Width: 19 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.