




Neon Flex Strip 3m

Light can shape your mood, and now you can shape your light, with bendable Neon Flex Strips from WiZ. With 3 metres of flexible light strip to play work, we're sure you can create clever and delightful shapes to beautify any room. Set the mood with neon gradient colour effects. Wi-Fi controllable, of course, using the WiZ app, WiZ remote or your voice.

PRODUCT HIGHLIGHTS

- Full colour
- Low Voltage
- IP20/Silicon



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Control with any Matter smart home platform

This product is Matter-certified, allowing easy control through Google Home, Amazon Alexa, Apple Home or any other Matter-based smart home platform of your choice.




Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and get the lights to turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.




Millions of colours and changing light modes to make your day

Choose any light colour you like or simply apply a dynamic light mode that we've designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



Control smart lighting the way you like it

WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control or by using the existing wall switch to toggle between two favourite modes. Works with Google Home, Alexa and Siri Shortcuts.



Gradient colours in a single strip

Set the mood with flexible light strips that offer gradient effects. Dynamic light modes let you create the right ambience for beautifying any room.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Dimmable: Yes

DESIGN AND FINISHING

Colour: White
Material: Plastic

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 15,000

EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: Yes
LED integrated: Yes
On/off switch on wire: Yes
Power adapter included: Yes
Remote control included: No

LIGHT CHARACTERISTICS

Colour rendering index (CRI): -
Colour temperature: NA
Warm-up time to 60% light: 2

STRING LIGHT/LIGHTSTRIP

Driver efficiency in full load: 80
Driver no load power: 0.25

MISCELLANEOUS

Especially designed for: Living Room
Entertainment room Bedroom
Children's room

OTHER CHARACTERISTICS

Lamp current: 125 mA

POWER CONSUMPTION

Power factor: 0.7
Voltage: 220-240 V
Power Consumption: 20

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.6 kg
Overall height: 17 mm
Overall length: 3,000 mm
Overall width: 10 mm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Total lumen output fixture: NA
Light colour: RGB
Wattage bulb included: 24
IP code: IP20 | Finger-protected
Class of protection: Class II – Double Insulated

WHAT'S SUPPORTED

Compatible with Effects feature: Yes
WiFi: Wireless G
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth
WiFi (2.4GHz)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8720169072534
Net weight: 0.6 kg
Gross weight: 0.9 kg
Height: 8.7 cm
Length: 22.4 cm
Width: 22.4 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.