




Portrait Desk Lamp



One light, so many uses! The multifunctional WiZ Portrait smart desk light offers dual light zones, perfect for task lighting at your desk, video calls, and even creating relaxing bedside light. Simply rotate the head to switch from desk lighting to video call lighting. A specially designed diffuser generates soft, adjustable ring light to make you look your best online. The embedded brightness sensor detects ambient light levels and automatically adjusts task lighting to reduce eye strain when working long hours. The simple and clean geometrical design fits well with any decor. The Portrait smart desk light plays well with the other lights in your WiZ ecosystem, with the easy control you've come to expect. Use the WiZ app, the WiZmote, or your voice to create the perfect ambience anywhere at home.

PRODUCT HIGHLIGHTS

- Tunable white
- Auto brightness adjustment
- Dual zone light effect



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Control with any Matter smart home platform

This product is Matter-certified, allowing easy control through Google Home, Amazon Alexa, Apple Home or any other Matter-based smart home platform of your choice.



Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and get the lights to turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energising cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



Dim your smart lights even without a dimmer

Simply adjust lights to your desired brightness level using your smartphone, the WiZ control accessory or just your voice. No need to install an expensive dimmer!



Dual light zones for focus, video calls or ambience

Dual light zones make the WiZ Portrait desk lamp multifunctional. When oriented horizontally, use the downwards light for focus and the upwards light for ambience. When oriented vertically, use the front light for video calls and the back light for ambience. One lamp, so many uses!



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: Rectangle
Dimmable: Yes

DESIGN AND FINISHING

Colour: White
Material: Plastic

DURABILITY

Average life (at 2.7 hrs/day): 25 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 25,000

EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: Yes
LED integrated: Yes
On/off switch on wire: No
Remote control included: No

LIGHT CHARACTERISTICS

Colour consistency: 6 SDCM
Colour rendering index (CRI): ≥ 90
Colour temperature: 2700-6500 K
Warm-up time to 60% light: 2
Luminous efficacy (rated) (nom.): 60 lm/W

MISCELLANEOUS

Especially designed for: Children's room Study

OTHER CHARACTERISTICS

Lamp current: 2000 mA

POWER CONSUMPTION

Voltage: 5 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 1.4 kg
Overall height: 380 mm
Overall length: 204 mm
Overall width: 195 mm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Total lumen output fixture: 600
Light colour: 2700-6500
Wattage bulb included: 10
IP code: IP20 | Finger-protected
Class of protection: Class III – Safe
Extra Low Voltage

WHAT'S SUPPORTED

Compatible with Effects feature: Yes
WiFi: Wireless G
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth
WiFi (2.4GHz)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8720169072695
Net weight: 1.46 kg
Gross weight: 1.73 kg
Height: 41.5 cm
Length: 21.3 cm
Width: 24.3 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.