



# Candle 40 W C37 E14 x3



The WiZ LED full-color candle-shape bulb brings smart lighting for your daily living. Perfect for any decorative fixtures with E14 medium base. Create the ambience of your choice with 16 million colours, as well as warm to cool white light. You can set schedules to turn lights on and off according to your daily or weekly routines, control with your smartphone or your voice and have remote access to your lights even when you're away. WiZ lights connect to your existing Wi-Fi, no additional hardware is needed.

## PRODUCT HIGHLIGHTS

- Full colour smart bulb
- Up to 470 lumens
- Easy plug and play
- Control with app or voice



### **Easy plug-and-play. Works with your existing Wi-Fi.**

WIZ works with your existing Wi-Fi router, no additional gateway is needed. Simply plug in your new light, download the WIZ app and you're ready to go!

### **Voice control with Google Assistant, Alexa or Siri Shortcuts**

Get hands-free control of your lights by using your voice and Google Assistant, Amazon Alexa or Siri Shortcuts. Use simple voice commands to turn lights on or off, brighten and dim, change colour and set custom light Scenes.

### **Control from anywhere with your smartphone.**

Control your WIZ lights wherever you are with smartphone. No need to worry if you've left your lights on before leaving home. WIZ app is available for iOS and Android.



### **Set up lights to follow your own schedule**

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.

### **Energy monitoring**

The WIZ app keeps records of the energy consumption of your lights. View your weekly or daily report and plan your lighting wisely for optimised energy consumption at home.



### **Millions of colours and changing light modes to make your day**

Choose any light colour you like or simply apply a dynamic light mode that we've designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



# SPECIFICATIONS

## BULB CHARACTERISTICS

Intended use: Indoor  
Lamp shape: C37  
Socket: E14  
Type of glass: Frosted  
Dimmable: Yes

## LAMP DIMENSIONS

Weight: 0.135 kg

## DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)  
Lumen maintenance factor: 70%  
Number of switch cycles: 50,000  
Nominal lifetime: 15,000

## LIGHT CHARACTERISTICS

Colour consistency: 6 SDCM  
Colour rendering index (CRI):  $\geq 90$   
Colour temperature: 2200-6500 K  
Light Colour Category: Full colour  
Nominal luminous flux: 470 lm  
Starting time:  $< 0.5$  s  
Warm-up time to 60% light: Instant full light  
Luminous efficacy (rated) (nom.): 95 lm/W

## OTHER CHARACTERISTICS

Lamp current: 40 mA

## PACKAGING INFORMATION

EAN: 8720169075672  
EOC: 872016907567200  
Product title: Wi-Fi BLE 40W C37 E14  
922-65 RGB 3CT6

## POWER CONSUMPTION

Power factor: 0.51  
Voltage: 220-240 V  
Wattage equivalent: 40 W  
Energy efficiency label (EEL): F  
Power Consumption: 4.9 W  
Energy consumption kWh/1,000 hours: 5

## PRODUCT DIMENSIONS AND WEIGHT

Overall height: 116 mm  
Overall length: 116 mm  
Overall width: 39 mm

## RATED VALUES

Rated lifetime: 15,000  
Rated luminous flux: 470 lm  
Rated power: 4.9 W

## TECHNICAL SPECIFICATIONS

Frequency: 50-60  
EPREL Registration Number: 1877836  
Flux measurement reference: Sphere

## WHAT'S SUPPORTED

Compatible with Effects feature: Yes  
WiFi: Wireless G  
Defined support period: Minimum of 60 months after introduction date  
Max. number of accessories: 9999  
Communication protocol: Bluetooth WiFi (2.4GHz)

## PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8720169075672  
Net weight: 0.14 kg  
Gross weight: 0.22 kg  
Height: 15.5 cm  
Length: 7 cm  
Width: 14 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.