



AMZ WFB 50W GU10 927-65 TW 3CT/6



Bring human-centric lighting into your living and working environments with this smart WiZ LED GU10 spot beam bulb. Apply different shades of warm to cool white to help you focus or relax. You can set a schedule to turn lights on and off according to your daily or weekly routines, control with your smartphone or your voice and have remote access to your lights even when you're away. WiZ lights connect to your existing Wi-Fi, no additional hardware is needed.

PRODUCT HIGHLIGHTS

- Tunable white smart bulb
- Up to 345 lumens
- Easy plug and play
- Control with app or voice



Easy plug-and-play. Works with your existing Wi-Fi.

WIZ works with your existing Wi-Fi router, no additional gateway is needed. Simply plug in your new light, download the WIZ app and you're ready to go!

Energy monitoring

The WIZ app keeps records of the energy consumption of your lights. View your weekly or daily report and plan your lighting wisely for optimised energy consumption at home.

Control from anywhere with your smartphone.

Control your WIZ lights wherever you are with smartphone. No need to worry if you've left your lights on before leaving home. WIZ app is available for iOS and Android.

Voice control with Google Assistant, Alexa or Siri Shortcuts

Get hands-free control of your lights by using your voice and Google Assistant, Amazon Alexa or Siri Shortcuts. Use simple voice commands to turn lights on or off, brighten and dim, change colour and set custom light Scenes.

Smart dimming via app, voice or dimmer

Dim your lights to your desired brightness level via your smartphone, the WIZmote or your voice. No need to install an expensive dimmer.



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: PAR16
Socket: GU10
Technology: Smart Wi-Fi
Type of glass: Frosted
Dimmable: Wireless Dim

LAMP DIMENSIONS

Height: 5.8 cm
Weight: 0.15 kg
Width: 5 cm

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 15,000 h

LIGHT CHARACTERISTICS

Beam angle: 36 degree(s)
Colour consistency: 6 SDCM
Colour rendering index (CRI): 90
Colour temperature: 2700-6500 K
Light Colour Category: Tunable white
Nominal luminous flux: 345 lm
Starting time: <0.5 s
Warm-up time to 60% light: Instant full light

OTHER CHARACTERISTICS

Lamp current: 40 mA
Efficacy: 73 lm/W

PACKAGING INFORMATION

EAN: 8720169075719
EOC: 872016907571900
Product title: AMZ WFB 50W GU10
927-65 TW 3CT6

POWER CONSUMPTION

Power factor: 0.51
Voltage: 220-240 V
Wattage: 4.7 W
Wattage equivalent: 50 W

PRODUCT DIMENSIONS AND WEIGHT

Length: 5.8 cm

RATED VALUES

Rated beam angle: 36 degree(s)
Rated lifetime: 15,000 h
Rated luminous flux: 345 lm
Rated peak intensity: 550 cd
Rated power: 4.7 W

TECHNICAL SPECIFICATIONS

Frequency: 50-60 Hz



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.