

## Wall Light Classic



Classic rectangular look, futuristic performance with these weatherproof mains voltage outdoor wall lights. Bathe your front garden, back garden, balcony or porch with a whopping 1,000 lumens of beautiful dynamic colour and tunable white light. Works with your existing Wi-Fi and WIZ lamps and luminaires.

## PRODUCT HIGHLIGHTS

- Full colour
- Mains Voltage
- Weather-proof




### **Instant setup for all your smart home functionalities**

Access all smart features instantly, simply by connecting your new lights to your existing Wi-Fi. You can control lights when you're away from home and set schedules to turn them on and off automatically. All without needing to install additional hardware. Keep the controller within Wi-Fi range, and all linked lights will be fully controllable even out of Wi-Fi range.



### **Control with any Matter smart home platform**

This product is Matter-certified, allowing easy control through Google Home, Amazon Alexa, Apple Home or any other Matter-based smart home platform of your choice.



### **Always feel safe and secure with automated outdoor lights**

Schedule your outdoor lights to turn on every day before you get home, so that you can clearly see your environment and feel safe. Set your lights to turn off automatically in the morning, or when they are not necessary, and save energy.



### **Create your perfect light scene**

Make your own mix of different colour and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



### **Beautify your garden with millions of colours and dynamic modes**

Choose from millions of light colours, from energising cool white to soft warm white, and create the best ambience for your outdoor activities. Or simply apply a preset dynamic light mode like Ocean, Forest or Party to create an amazing atmosphere and lift the mood.



### **Control your outdoor lighting the way you like it**

WiZ gives you many options to control your smart lights. Simply adjust lights with your smartphone or your voice from wherever you are. Works with Google Home, Alexa and Siri shortcuts.



# SPECIFICATIONS

## BULB CHARACTERISTICS

Intended use: Outdoor  
Dimmable: Yes

## DESIGN AND FINISHING

Colour: Black  
Material: Metal Plastic

## DURABILITY

Average life (at 2.7 hrs/day): 25 year(s)  
Lumen maintenance factor: 70%  
Number of switch cycles: 50,000  
Nominal lifetime: 25,000

## EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: Yes  
LED integrated: Yes  
LED lamp(s) included: Yes  
Remote control included: No

## LIGHT CHARACTERISTICS

Colour consistency: 6 SDCM  
Colour rendering index (CRI):  $\geq 80$   
Colour temperature: 2700-5000 K  
Warm-up time to 60% light: 2  
Luminous efficacy (rated) (nom.): 63 lm/W

## MISCELLANEOUS

Especially designed for: Garden  
Balcony

## OTHER CHARACTERISTICS

Lamp current: 50 mA

## POWER CONSUMPTION

Power factor: 0.7  
Voltage: 220-240 V

## PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.79 kg  
Overall height: 228 mm  
Overall length: 227 mm  
Overall width: 170 mm

## SERVICE

Warranty: 2 year(s)

## TECHNICAL SPECIFICATIONS

Lumen output bulb included: 1,000  
Total lumen output fixture: 600  
Light colour: 2700-5000 (RGB)  
Wattage bulb included: 9.5  
Maximum wattage replacement bulb: 9.5  
IP code: IP44 | Wire-protected and splash-proof  
Class of protection: Class I – Earthed  
Light source replaceable: No  
Number of light sources: 1

## WHAT'S SUPPORTED

Compatible with Effects feature: Yes  
WiFi: Wireless G  
Defined support period: Minimum of 60 months after introduction date  
Max. number of accessories: 9999  
Communication protocol: Bluetooth WiFi (2.4GHz)

## PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8720169076181  
Net weight: 0.79 kg  
Gross weight: 1.17 kg  
Height: 29.6 cm  
Length: 19.7 cm  
Width: 25.2 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.