



Bulb 60W A60 E27



Not all moments are created equal, and neither are all smart bulbs. This WiZ light might have a basic A60 shape, but it gives you something truly special: tunable white LED light for all your needs and moods. Schedule cool light when you need to focus, or cosy light when you want to relax – whatever works for you to live your best, most enjoyable life at home. All Wi-Fi controllable using the WiZ app, WiZ remote or your voice.

PRODUCT HIGHLIGHTS

- Tunable white smart bulb
- Up to 806 lumens
- Easy plug and play
- Control with app or voice



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Control with any Matter smart home platform

This product is Matter-certified, allowing easy control through Google Home, Amazon Alexa, Apple Home or any other Matter-based smart home platform of your choice.




Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Activate devices with motion without using a sensor

WiZ's SpaceSense technology transforms your devices into motion sensors. Activate the SpaceSense feature in the WiZ app and have lights and devices turn on and off automatically, with motion detection. A minimum of two WiZ devices in a room is needed for the SpaceSense feature to work.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energising cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: A60
Socket: E27
Technology: Smart Wi-Fi
Type of glass: Frosted
Dimmable: Yes

LAMP DIMENSIONS

Height: 11.1 cm
Weight: 0.05 kg
Width: 6 cm

DURABILITY

Average life (at 2.7 hrs/day): 25 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 25,000

LIGHT CHARACTERISTICS

Colour consistency: 6 SDCM
Colour rendering index (CRI): ≥ 80
Colour temperature: 2700-6500 K
Light Colour Category: Tunable white
Nominal luminous flux: 806 lm
Starting time: < 0.5 s
Warm-up time to 60% light: Instant full light

OTHER CHARACTERISTICS

Lamp current: 65 mA
Efficacy: 100 lm/W

PACKAGING INFORMATION

EAN: 8720169076945
EOC: 872016907694500
Product title: Wi-Fi BLE 60W A60 E27
827-65 TW 1PF/6

POWER CONSUMPTION

Power factor: 0.5
Voltage: AC 220-240 V
Wattage: 8 W
Wattage equivalent: 60 W
Energy efficiency label (EEL): F

PRODUCT DIMENSIONS AND WEIGHT

Length: 11.1 cm

RATED VALUES

Rated lifetime: 25,000
Rated luminous flux: 806 lm
Rated power: 8 W

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Frequency: 50-60 Hz
EPREL Registration Number: 1877823
Flux measurement reference: Sphere

THE BRIDGE

Max. number of accessories: 9,999

THE BULB

Communication protocol: Bluetooth
WiFi (2.4GHz)

WHAT'S SUPPORTED

Compatible with Effects feature: Yes
WiFi: Wireless G
Defined support period: Minimum of 60 months after introduction date

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8720169076945
Net weight: 0.05 kg
Gross weight: 0.09 kg
Height: 16 cm
Length: 7 cm
Width: 7 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.