



## Flex Strip 5m

Craft mesmerising shapes with Smart Flex Strip's bendable design, adding flair to any room. With its vibrant colours and effects, you can effortlessly set the perfect mood for any occasion. Whether through the WiZ App, voice commands or remote control, personalising your lighting experience has never been easier. Transform your living space effortlessly and sculpt light in ways you never thought possible with Smart Flex Strip.

## PRODUCT HIGHLIGHTS

- Full colour
- Low Voltage
- IP20/Silicon



## Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



## Control with any Matter smart home platform

This product is Matter-certified, allowing easy control through Google Home, Amazon Alexa, Apple Home or any other Matter-based smart home platform of your choice.



## Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and get the lights to turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.



## Millions of colours and changing light modes to make your day

Choose any light colour you like or simply apply a dynamic light mode that we've designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.

## Sync lights to music

Dive into the rhythm with our Music Sync feature. Effortlessly synchronise your lights to your favorite tunes. Just remember, keep your mobile device near the speaker for perfect harmony between sound and light.

## Gradient colours in a single strip

Set the mood with flexible light strips that offer gradient effects. Dynamic light modes let you create the right ambience for beautifying any room.



# SPECIFICATIONS

## BULB CHARACTERISTICS

Intended use: Indoor  
Dimmable: Yes

## DESIGN AND FINISHING

Colour: White  
Material: Plastic

## DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)  
Lumen maintenance factor: 70%  
Number of switch cycles: 50,000  
Nominal lifetime: 15,000

## EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: Yes  
LED integrated: Yes  
On/off switch on wire: Yes  
Power adapter included: Yes  
Remote control included: No

## LIGHT CHARACTERISTICS

Colour rendering index (CRI): -  
Colour temperature: NA  
Warm-up time to 60% light: 2

## MISCELLANEOUS

Especially designed for: Living Room  
Entertainment room Bedroom  
Children's room

## OTHER CHARACTERISTICS

Lamp current: 125 mA

## POWER CONSUMPTION

Power factor: 0.7  
Voltage: 220-240 V  
Power Consumption: 19

## PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.655 kg  
Overall height: 13 mm  
Overall length: 5,000 mm  
Overall width: 6 mm

## SERVICE

Warranty: 2 year(s)

## TECHNICAL SPECIFICATIONS

Total lumen output fixture: NA  
Light colour: RGB  
Wattage bulb included: 22  
IP code: IP20 | Finger-protected  
Class of protection: Class II – Double  
Insulated

## WHAT'S SUPPORTED

Compatible with Effects feature: Yes  
WiFi: Wireless G  
Defined support period: Minimum of 60 months after introduction date  
Max. number of accessories: 9999  
Communication protocol: Bluetooth WiFi (2.4GHz)

## PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8720169077300  
Net weight: 0.66 kg  
Gross weight: 1.02 kg  
Height: 9.3 cm  
Length: 23.7 cm  
Width: 23.7 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.