




Square Panel 17 W



Light up your life with the WiZ Smart Ceiling Panel Light. Choose between minimalist black and classic white – whichever works best with your decor! Enjoy all of the convenience and energy savings of an LED fixture with tunable white light. Try cool daylight for concentrating or cosy candlelight for relaxing and everything in between. Plus, you can control it 100% remotely with the WiZ app or your voice.


PRODUCT HIGHLIGHTS

- Full colour
- Dimensions: 395
- IP20/Plastic/Black



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Create your perfect light scene

Make your own mix of different colour and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



Millions of colours and changing light modes to make your day

Choose any light colour you like or simply apply a dynamic light mode that we've designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energising cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



Control your smart lights from anywhere

No need to worry if lights were left on while no one's at home. Simply turn them off from wherever you are, with your smartphone.



Slim, sleek design for your ceiling

This light's minimalistic design and slim shape make it an ideal match to any interior style.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Dimmable: Yes

DESIGN AND FINISHING

Colour: Black
Material: Plastic

DURABILITY

Average life (at 2.7 hrs/day): 20 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 20,000
Nominal lifetime: 20,000

EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: Yes
LED integrated: Yes
Remote control included: No

LIGHT CHARACTERISTICS

Colour consistency: 6 SDCM
Colour rendering index (CRI): ≥80
Colour temperature: 2200-6500 K
Warm-up time to 60% light: 2
Luminous efficacy (rated) (nom.): 129
lm/W

MISCELLANEOUS

Especially designed for: Living Room
Kitchen Dining Room Bedroom

OTHER CHARACTERISTICS

Lamp current: 150 mA

POWER CONSUMPTION

Power factor: 0.5
Voltage: 220-240 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 1.8 kg
Overall height: 37 mm
Overall length: 395 mm
Overall width: 395 mm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Total lumen output fixture:
2200(@2700K)
Light colour: 2200-6500 (RGB)
Wattage bulb included: 17
IP code: IP20 | Finger-protected
Class of protection: Class II – Double
Insulated

WHAT'S SUPPORTED

Compatible with Effects feature: Yes
WiFi: Wireless G
Defined support period: Minimum of
60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth
WiFi (2.4GHz)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8720169077980
Net weight: 1.9 kg
Gross weight: 2.6 kg
Height: 45.2 cm
Length: 5.9 cm
Width: 44.9 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.