



## LED Strip 4m

Our 4 m RGB light strips are designed to fit and beautify large spaces with over 16 million solid colours, static and dynamic modes and smart features. Just cut them as you wish, place them on any surface thanks to their non-damaging adhesive and use the intuitive WiZ app to control them through your existing Wi-Fi. Static and dynamic light modes, smart dimming, and light scheduling put you in charge of your whole system – even when you're away from home. Works with Google Home, Amazon Alexa and Apple HomeKit for the ultimate in ease of use.

## PRODUCT HIGHLIGHTS

- Full colour
- IP20/Plastic



### Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!




### Control with any Matter smart home platform

This product is Matter-certified, allowing easy control through Google Home, Amazon Alexa, Apple Home or any other Matter-based smart home platform of your choice.




### Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



### Activate devices with motion without using a sensor

WiZ's SpaceSense technology transforms your devices into motion sensors. Activate the SpaceSense feature in the WiZ app and have lights and devices turn on and off automatically, with motion detection. A minimum of two WiZ devices in a room is needed for the SpaceSense feature to work.



### Millions of colours and changing light modes to make your day

Choose any light colour you like or simply apply a dynamic light mode that we've designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



### Control your smart lights from anywhere

No need to worry if lights were left on while no one's at home. Simply turn them off from wherever you are, with your smartphone.



# SPECIFICATIONS

## BULB CHARACTERISTICS

Intended use: Indoor  
Dimmable: Yes

## DESIGN AND FINISHING

Colour: White  
Material: Plastic

## DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)  
Lumen maintenance factor: 70%  
Number of switch cycles: 50,000  
Nominal lifetime: 15,000

## EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: Yes  
LED integrated: Yes  
On/off switch on wire: Yes  
Power adapter included: Yes  
Remote control included: No

## LIGHT CHARACTERISTICS

Colour rendering index (CRI): -  
Colour temperature: NA  
Warm-up time to 60% light: 2

## MISCELLANEOUS

Especially designed for: Living Room  
Entertainment room Bedroom  
Children's room

## OTHER CHARACTERISTICS

Lamp current: 40 mA

## POWER CONSUMPTION

Power factor: 0.7  
Voltage: 220-240 V  
Power Consumption: 5.3

## PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.162 kg  
Overall height: 2.1 mm  
Overall length: 4,000 mm  
Overall width: 10 mm

## SERVICE

Warranty: 2 year(s)

## TECHNICAL SPECIFICATIONS

Total lumen output fixture: NA  
Light colour: RGB  
Wattage bulb included: 6.5  
IP code: IP20 | Finger-protected  
Class of protection: Class II – Double Insulated

## WHAT'S SUPPORTED

Compatible with Effects feature: Yes  
WiFi: Wireless G  
Defined support period: Minimum of 60 months after introduction date  
Max. number of accessories: 9999  
Communication protocol: Bluetooth WiFi (2.4GHz)

## PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8720169078246  
Net weight: 0.15 kg  
Gross weight: 0.34 kg  
Height: 21.8 cm  
Length: 8.2 cm  
Width: 18.9 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.