

# PHILIPS

Filament Bulb Clear  
60W A60 B22

Ultra Efficient

2700K

840 lm

50000 h



8720169187672



## UltraEfficient lamp, our most energy-efficient LED bulbs

Philips UltraEfficient LED lamps provide beautiful light, offer an exceptionally long lifetime of 50,000 hours, and deliver immediate and significant energy savings. Reduce the frequency of lamp replacements and enjoy light that's easy on the eyes with our trusted EyeComfort design.

### High-quality light

- Designed for the comfort of your eyes

### Designed to last longer and save more energy

- Everyday switch on, save energy
- Long life bulb – Lasts up to 50 years

# Highlights

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Everyday switch on, save energy



Our UltraEfficient LEDs are at least 50% more energy-efficient than standard Philips LEDs, saving you energy every day

## Long life bulb – Lasts up to 50 years



Avoid the hassle of frequent light bulb replacements. With a lifetime of up to 50,000 hours, our UltraEfficient LEDs last 3.5 times longer than standard Philips LEDs, so you can enjoy a perfect lighting solution for more than 50 years.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: B22
- Dimmable: No
- Lamp Finish: Clear
- Bulb material: Glass

## Durability

- Number of switch cycles: 500,000
- Nominal lifetime: 50,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 300 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 840 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 827 | CCT of 2700K
- Luminous efficacy (rated) (nom.): 210

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort, UltraEfficient

## Packaging information

- EAN: 8720169187672
- EOC: 872016918767200
- Product title: LED CLA 60W A60 B22 2700K CL UE SRT4

**Power consumption**

- Power factor: 0.4
- Voltage: AC 220-240 V
- Wattage equivalent: 60 W
- Energy efficiency label (EEL): A
- Power: 4 W
- Energy consumption kWh/1,000 hours: 4

**Product dimensions and weight**

- Overall height: 102 mm
- Overall length: 102 mm
- Overall width: 60 mm

**Technical specifications**

- Frequency: 50-60
- EPREL Registration Number: 1442610
- Can it be used in closed luminaires: No

**Packaging dimensions and weight**

- EAN/UPC - product: 8720169187672
- Net weight: 0.03 kg
- Gross weight: 0.05 kg
- Height: 14.6 cm
- Length: 6.5 cm
- Width: 6.3 cm



Issue date: 2026-02-17  
Version: 0.358

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)