

# PHILIPS

Filament Bulb Clear  
75W A60 E27

Ultra Efficient

4000K

1095 lm

50000 h



8720169187894



## Bright LED lighting with excellent light quality

A Philips LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs straight away and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### High-quality light

- Designed for the comfort of your eyes

### Designed to last longer and save more energy

- Everyday switch on, save energy
- Long life bulb – Lasts up to 50 years

# Highlights

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Everyday switch on, save energy



Our UltraEfficient LEDs are at least 50% more energy-efficient than standard Philips LEDs, saving you energy every day

## Long life bulb – Lasts up to 50 years



Avoid the hassle of frequent light bulb replacements. With a lifetime of up to 50,000 hours, our UltraEfficient LEDs last 3.5 times longer than standard Philips LEDs, so you can enjoy a perfect lighting solution for more than 50 years.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

## Lamp dimensions

- Height: 10.4 cm
- Width: 6 cm

## Durability

- Number of switch cycles: 500,000
- Nominal lifetime: 50,000 h

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 300 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Nominal luminous flux: 1095 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 840 | CCT of 4000K

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort, UltraEfficient

## Other characteristics

- Efficacy: 210 lm/W

## Packaging information

- EAN: 8720169187894
- EOC: 872016918789400
- Product title: LED CLA 75W A60 E27 4000K CL UE SRT4

#### Power consumption

- Power factor: 0.4
- Voltage: AC 220–240 V
- Wattage: 5.2 W
- Wattage equivalent: 75 W
- Energy efficiency label (EEL): A

#### Product dimensions and weight

- Length: 10.4 cm

#### Technical specifications

- Frequency: 50–60 Hz
- EPREL Registration Number: 1442621

#### Packaging dimensions and weight

- EAN/UPC – product: 8720169187894
- Net weight: 0.03 kg
- Gross weight: 0.05 kg
- Height: 14.6 cm
- Length: 6.5 cm
- Width: 6.3 cm



Issue date: 2025-04-17  
Version: 0.468

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)