

# PHILIPS

Filament Bulb Amber  
40W G125 E27

LED


7W-40W

E27

Flame



8720169191198



## Designed to be seen

The new Deco collection transforms your home with a perfect blend of (warm) white light and a lean, minimalistic lighting experience.

### Choose a simple replacement for your old lamps

- Similar shape and size as standard incandescent bulbs

### Choose for a sustainable solution

- Long-life tubes – Lasts up to 15 years
- Saves up to 90% Energy

### Designed to be seen, looks good on and off

- Vintage style LED

# Highlights

## Replaces standard incandescents



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light tubes and enjoy a perfect lighting solution for over 15 years.

## Saves up to 90% Energy



Enjoy the energy saving of LEDs without sacrificing light quality. Instantly save over 90% in energy by replacing your existing incandescent or halogen lamps

## Vintage (2,000 K & 2,200 K)

Imagine the vintage look of traditional lighting with the benefits of LED. With Philips Vintage LED filament bulbs, you can have the classic look you love, with the energy-efficiency you need. Gives the traditional colour and amber glow of old-fashioned incandescent lighting. The clear amber-tinted glass bulb, brass finish base and retro styling of the LED filament add a vintage flair to the decorative lighting in your home. The intricate swirling filament offers a cosy and warm ambience.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional globe
- Socket: E27
- Lamp Finish: Amber
- Dimmable: No
- Bulb material: Glass

## Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- LED integrated: Yes

#### Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 1800 K
- Nominal luminous flux: 470 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 818 | CCT of 1800K
- Luminous efficacy (rated) (nom.): 67

#### Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Decorative

#### Packaging information

- EAN: 8720169191198
- EOC: 872016919119800
- Product title: LED G125 40W 1800K E27 NDSRT Amber 1PF

#### Power consumption

- Power factor: 0.5
- Voltage: AC 230 V
- Wattage equivalent: 40
- Power: 7
- Energy consumption kWh/1,000 hours: 7

#### Product dimensions and weight

- Overall height: 178 mm
- Overall length: 178 mm
- Overall width: 125 mm

#### Technical specifications

- Frequency: 50-60
- Bulb technology: LED

#### Packaging dimensions and weight

- EAN/UPC - product: 8720169191198
- Net weight: 0.1 kg
- Gross weight: 0.2 kg
- Height: 22.6 cm
- Length: 13 cm
- Width: 13 cm



Issue date: 2026-03-21  
Version: 0.409

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)