

# PHILIPS

Wincel Ceiling Light  
40 W

Ceiling Lights

2700-6500K

White

Dimmable; Remote Control



8720169196131



## Set your desired ambience at your fingertips

With just a few simple clicks on the remote control, the Philips LED All-in-one ceiling light gives you the ultimate flexibility and convenience to personalise your light settings with ease. A comfortable light that's easy on your eyes. Create desired ambience with a light that understands your needs.

### Premium quality

- EyeComfort – light that's easy on the eyes

### Control

- Tunable – from warm white to cool daylight
- Brightness control with memory function
- 4 pre-set scenes
- A remote control provides easy control for the light settings at up to 10 metres
- Wall-mountable remote-control

# Highlights

## EyeComfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output and colour for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

## Tunable – from warm white to cool daylight

Tunable lighting lets you change the colour of light to match your mood or activity. Warm white is ideal for relaxation, cool daylight for invigorating focus.

## Brightness control with memory function

Memorises the specific brightness levels you prefer.

## 4 pre-set scenes

Enjoy different ambiances with the convenience of pre-set light scenes for every occasion.

## A remote control provides easy control for the light settings at up to 10 metres

Turn lights on or off or change brightness and colour from up to 10 metres away with this remote control.

## Wall-mountable remote-control

With the included bracket, you can mount your remote wherever you need an additional switch – no wiring required.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round
- Dimmable: Yes

## Design and finishing

- Colour: White
- Material: Plastic

## Durability

- Average life (at 2.7 hrs/day): 20 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 15,000
- Nominal lifetime: 20,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Dimmable with remote control: Yes
- LED integrated: Yes
- Remote control included: Yes

## Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2700–6500 K
- Warm-up time to 60% light: 2
- Luminous efficacy (rated) (nom.): 107

## Miscellaneous

- Especially designed for: Kitchen, Bedroom, Dining Room, Garage, Living Room, Office
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- Extra Features: Dimmable, Remote control

## Other characteristics

- Lamp current: 210 mA

## Power consumption

- Power factor: 0.9

#### Product dimensions and weight

- Net weight: 1.3 kg
- Overall height: 70 mm
- Overall length: 478 mm
- Overall width: 478 mm

#### Service

- Warranty: 5 year(s)

#### Technical specifications

- Diameter: 478 mm
- Total lumen output fixture: 4300
- Light colour: Tunable white light
- Mains power: AC 220-240
- IP code: IP20 | Finger-protected
- Class of protection: Class I – Earthed

#### Packaging dimensions and weight

- EAN/UPC – product: 8720169196131
- Net weight: 1.19 kg
- Gross weight: 2.01 kg
- Height: 9.1 cm
- Length: 56.3 cm
- Width: 57 cm



Issue date: 2026-03-07  
Version: 0.350

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)