

# PHILIPS

Meson Recessed  
Light 215mm 23.5W

Recessed Lights

Meson

white

8720169231085



## Comfortable light with a slimmer fit

Light up your space with Philips EyeComfort LED Downlight that provides a comfortable light source and ease to your eyes.

### Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

### Durability

- Long life span up to 15,000 hours

### High-quality LED light that lasts for decades

- Reduced glare. Increased comfort.

# Highlights

## Suitable for low ceilings Slim design Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

## EyeComfort with interlaced optics

Interlaced optics technology enhances the overall lighting experience in your everyday life. Imprinted with 3D patterns to help diffuse light, the micro-lens technology produce an

even distribution of light which reduces glare significantly. This illumination is not only a soft and uniform light which brings more comfort to your eyes, but it also cleverly redistributes light for less glaring illumination in the lit area.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

## Design and finishing

- Colour: White
- Material: Plastic

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 7,500
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 100
- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Warm-up time to 60% light: 2
- Luminous efficacy (rated) (nom.): 80

## Miscellaneous

- Especially designed for: Kitchen, Bedroom, Dining Room, Living Room, Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes

## Other characteristics

- Lamp current: 165 mA

## Power consumption

- Power factor: 0.5

## Product dimensions and weight

- Net weight: 0.154 kg
- Recessed distance: 117 mm
- Overall height: 35 mm
- Overall length: 215 mm
- Overall width: 215 mm
- Recessed ceiling cutout: 20.0 cm x 20.0 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Diameter: 215 mm
- Total lumen output fixture: 2550
- Bulb technology: LED
- Light colour: Cool white light
- Mains power: AC 220-240
- Fixture dimmable: No
- Wattage bulb included: 23.5
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated

**Packaging dimensions and weight**

- EAN/UPC - product: 8720169231085
- Net weight: 0.31 kg
- Gross weight: 0.43 kg
- Height: 8.1 cm
- Length: 21.7 cm
- Width: 21.7 cm



Issue date: 2026-03-21  
Version: 0.347

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)