

PHILIPS

LEDtube Mains T5

LED

8 W-14 W

G5

White



8720169249417



Durable LED task lighting with excellent light quality

Upgrading to Philips LED tubes is a fast and easy way to replace your old fluorescent tubes with modern and efficient LED technology. This Philips LED tube is perfect for places that require a lot of light.

High-quality light

- Designed for the comfort of your eyes
- No hum buzz

Choose for a sustainable solution

- Contains no mercury
- A superior LED light solution to replace various form factors of ceiling luminaires, no matter the traditional light source or LED light source.

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

TLED No Hum/Buzz

Philips LED tubes do not create excessive noise while operating on a fluorescent ballast or by itself bypassing the ballast (MainsFit application)

Contains no mercury



Wide scope of replacement

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: T5
- Socket: G5
- Lamp Finish: Frosted
- Dimmable: No
- Bulb material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 35,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Beam angle: 200
- Colour rendering index (CRI): 80
- Colour temperature: 3000 K
- Nominal luminous flux: 1000 lm
- Warm-up time to 60% light: 0.5
- Colour Code: 830 | CCT of 3000K
- Luminous efficacy (rated) (nom.): 125

Miscellaneous

- Approval marks: RoHS compliance

Packaging information

- EAN: 8720169249417
- EOC: 872016924941700
- Product title: LED T5 600mm 8W G5 WH HE 1CT/4

Power consumption

- Power factor: 0.9
- Voltage: 220-240 V
- Energy efficiency label (EEL): E
- Power: 8
- Energy consumption kWh/1,000 hours: 8

Product dimensions and weight

- Overall height: 563 mm
- Overall length: 563 mm
- Overall width: 19 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Frequency: 50-60
- Bulb technology: LED
- EPREL Registration Number: 1476408
- Ballast Compatibility: Mains

Packaging dimensions and weight

- EAN/UPC - product: 8720169249417
- Net weight: 0.07 kg
- Gross weight: 0.11 kg
- Height: 56.3 cm
- Length: 2.9 cm
- Width: 2.9 cm



Issue date: 2026-03-21
Version: 0.340

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com