

PHILIPS

Kylis Wall Light
25W GU10 No-bulb

Outdoor luminaires

No bulb

Black

Water Resistant



8720169266551



Enjoy a beautiful garden with light

This outdoor light is designed around the latest trends and lifestyles to define the ambiance you have always desired.

Ease of use

- No bulb included

Bring design into your garden

- Choose outdoor wall lights

Premium quality

- High quality material

Designed for outdoors

- IP44 – weatherproof

Highlights

No bulb included

This luminaire comes without a bulb, which enables you to choose the light output which is best suited to the room and your personal taste. Choosing a Philips LED bulb will ensure a high quality and long-lasting light output.

Choose outdoor wall lights

Make the most of your outdoor space with this wall light, perfect for mounting close to your front door or on your terrace walls.

High quality material



This Philips outdoor lamp is made of high-quality materials with superior finishing. This ensures a solid and long-lasting product which is resistant to corrosion and stains in all weather conditions

IP44 – weatherproof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water – perfect for general outdoor use.

Specifications

Design and finishing

- Colour: Black
- Material: Metal

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Fully weatherproof: Yes
- LED integrated: No
- Motion sensor: No
- Solar Energy: No
- Warm White Light: No
- Centrepiece: No

Garden area

- Garden area: Garden and Patio

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Water Resistant

Product dimensions and weight

- Net weight: 0.45 kg
- Overall height: 118 mm
- Overall length: 90 mm
- Overall width: 78 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Mains power: 220–240 V
- Fixture dimmable: No
- Energy class included light source: not applicable
- Fitting/cap: GU10
- Maximum wattage replacement bulb: 25
- IP code: IP44
- Class of protection: Class I – Earthed
- Light source replaceable: Yes
- Number of light sources: 1

Packaging dimensions and weight

- EAN/UPC – product: 8720169266551
- Net weight: 0.45 kg
- Gross weight: 0.5 kg
- Height: 13 cm
- Length: 8.5 cm
- Width: 10 cm



Issue date: 2025-08-30
Version: 0.297

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com