

# PHILIPS

Laven Wall Light 6W

Outdoor luminaires

2700K

Black

Water Resistant



8720169266636



## Enjoy a beautiful garden with light

This outdoor light is designed around the latest trends and lifestyles to define the ambiance you have always desired. Available in warm or cool white light.

### Advanced LED light

- High-quality LED light

### Premium quality

- High quality material

### Designed for outdoors

- IP44 – weatherproof

### High-quality light

- Warm white light 2,700 K

# Highlights

## High-quality LED light

The LED light bulb delivered with this Philips lamp is a unique solution developed by Philips. It turns on instantly, enables an optimal light output and brings out vivid colours in your home.

## High quality material




This Philips outdoor lamp is made of high-quality materials with superior finishing. This ensures a solid and long-lasting product which is resistant to corrosion and stains in all weather conditions

## IP44 – weatherproof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water – perfect for general outdoor use.

## Warm white light 2,700 K



Did you know that different shades of white light are identified by different colour temperatures, measured in Kelvin (K)? Lower colour temperatures produce a warm, cosy white light, while higher colour temperatures produce a cool, more energising white light. This luminaire produces warm, relaxing light at 2,700 K.

# Specifications

## Design and finishing

- Colour: Black
- Material: Metal

## Durability

- Nominal lifetime: 25,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: No
- Solar Energy: No
- Centrepiece: No

## Garden area

- Garden area: Garden and Patio

## Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K

**Miscellaneous**

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Water Resistant

**Power consumption**

- Power: 6

**Product dimensions and weight**

- Net weight: 0.26 kg
- Overall height: 87 mm
- Overall length: 100 mm
- Overall width: 100 mm

**Service**

- Warranty: 2 year(s)

**Technical specifications**

- Total lumen output fixture: 720
- Bulb technology: LED
- Light colour: Warm white light
- Mains power: 220–240 V
- Fixture dimmable: No
- Energy class included light source: E
- IP code: IP44
- Class of protection: Class II – Double Insulated
- Light source replaceable: No

**The bulb**

- Software upgradable: No

**What's supported**

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

**Packaging dimensions and weight**

- EAN/UPC - product: 8720169266636
- Net weight: 0.26 kg
- Gross weight: 0.31 kg
- Height: 10 cm
- Length: 11 cm
- Width: 11 cm



Issue date: 2026-05-30  
Version: 0.295

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)