

PHILIPS

Fresco Recessed light 4.6W

Outdoor luminaires

2700K

Black

Water Resistant



8720169266858



Easily direct high-quality LED light wherever you want it

The Philips Fresco recessed spot has beautiful LED light to show garden features at their best or illuminate dark areas clearly. It is constructed from durable stainless steel, while the adjustable head allows for a directional beam.

Ease of use

- Adjustable spot head

Advanced LED light

- High-quality LED light

Premium quality

- Long-lasting, high-quality materials

Designed for outdoors

- IP23 – weatherproof

Highlights

Adjustable spot head



Direct the light where you want it most by simply adjusting, rotating or tilting the spot head of the lamp.

High-quality LED light

The LED light bulb delivered with this Philips lamp is a unique solution developed by Philips. It turns on instantly, enables an optimal light output and brings out vivid colours in your home.

Long-lasting, high-quality materials

This spot light is made of long-lasting, high-quality materials with superior finishing. This ensures a solid and durable product that will enhance and light up your home for many years to come.

IP23 – weatherproof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP23 rating means that it is designed to be protected against spraying water and ideal for lighting a veranda or a porch.

Specifications

Design and finishing

- Colour: Black
- Material: Metal

Durability

- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Fully weatherproof: No
- LED integrated: No

Garden area

- Garden area: Garden and Patio

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: No
- Extra Features: Water Resistant

Product dimensions and weight

- Net weight: 0.16 kg
- Recessed distance: 110 mm
- Overall height: 110 mm
- Overall length: 100 mm
- Overall width: 100 mm
- Recessed ceiling cutout: 8.0 cm x 8.0 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Total lumen output fixture: 355
- Bulb technology: LED
- Light colour: Warm white light
- Mains power: 220–240 V
- Fixture dimmable: No
- Energy class included light source: G
- Fitting/cap: GU10
- Wattage bulb included: 4.6
- IP code: IP20
- Class of protection: Class II – Double Insulated
- Light source replaceable: Yes
- Number of light sources: 1

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8720169266858
- Net weight: 0.16 kg
- Gross weight: 0.28 kg
- Height: 10 cm
- Length: 9 cm
- Width: 10 cm



Issue date: 2026-05-30
Version: 0.375

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com