

# PHILIPS

Security Securit  
8.7W

Outdoor luminaires

5000 K

Black

Sensor; Solar; Water Resistant



8720169269156



## Long-lasting solar-powered garden light for all seasons

Philips Nysil security light is a reliable solar light that lasts for a longer time, reduces energy consumption and supports sustainability.

### Easy installation

- No wiring required

### Sustainable light solutions

- Long lifetime up to 15,000 hours

### Advanced LED light

- High-quality LED light

### Premium quality

- High quality material

### Special characteristics

- Motion sensor, for convenience and reassurance

# Highlights

## No wiring required



This light is powered entirely by solar energy. No wiring is needed, making these lights easy to position and reposition anywhere in your garden or other outdoor area.

## High-quality LED light



These LED lights use a unique technology developed by Philips. They turn on instantly and produce optimal light output that brings out the vivid colours in your garden.

## Motion sensor, for convenience and reassurance



A motion sensor is included to welcome you when you return home or let you know when someone's coming.

## Long lifetime up to 15,000 hours



Reliable high-quality LED light lasts up to 15,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while enjoying the perfect garden light every night.

## High quality material



This Philips outdoor lamp is made of high-quality materials with superior finishing. This ensures a solid and long-lasting product which is resistant to corrosion and stains in all weather conditions

# Specifications

## Design and finishing

- Colour: Black
- Material: Plastic

## Durability

- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

**Extra feature/accessory incl.**

- Adjustable spot head: Adjustable – rise and fall
- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: Yes
- Diffused light effect: Yes
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: Yes
- Premium quality material: Yes
- Solar Energy: Yes
- Warm glow dimmable light: No
- Centrepiece: No

**Garden area**

- Garden area: Garden and Patio

**Light characteristics**

- Colour rendering index (CRI): 80
- Colour temperature: 5000 K

**Miscellaneous**

- Especially designed for: Garden, Patio
- Style: Contemporary
- EyeComfort: No
- Extra Features: Sensor, Solar, Water Resistant

**Power consumption**

- Power: 8.7

**Product dimensions and weight**

- Net weight: 0.47 kg
- Overall height: 168 mm
- Overall length: 293 mm
- Overall width: 117 mm

**Service**

- Warranty: 2 year(s)

**Technical specifications**

- Bulb technology: LED
- Light colour: Daylight
- Mains power: 4 V
- Fixture dimmable: No
- Energy class included light source: not applicable
- IP code: IP65
- Class of protection: Class III – Safe Extra Low Voltage
- Light source replaceable: No

**The bulb**

- Software upgradable: No

**What's supported**

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

**Packaging dimensions and weight**

- EAN/UPC – product: 8720169269156
- Net weight: 0.47 kg
- Gross weight: 0.65 kg
- Height: 18 cm
- Length: 14 cm
- Width: 23 cm

