

Extension cord 10m

Outdoor luminaires

GardenLink

Black

Low Voltage; Water Resistant



8720169269354



## A garden light that you can simply plug in, connect and enjoy

The Philips GardenLink low-voltage family offers a range of outdoor luminaires that you can easily and safely install. You can connect multiple lights to a single power supply and plug it into a standard socket, then easily add additional lights or reposition them whenever you like. Wiring is simple, and the low-voltage means that there's no danger of harm to you, your kids or your pets.

### **Ease of use**

- Compatible with all GardenLink luminaires and accessories
- Easy to install with Twist & Lock connectors

### **Safe to use**

- Extra safety with 24 V low voltage

### **Premium quality**

- High quality material

# Highlights

## Compatible with all GardenLink luminaires and accessories

Every GardenLink luminaire offers the same Twist & Lock connector for easy installation and connection. You can reposition the luminaires and accessories as your outdoor illumination needs change, adding light to every corner of your garden.

## Easy to install with Twist & Lock connectors

Super-easy installation and connection with the products' Twist & Lock connectors. Simply plug the lights in and enjoy!

## High quality material

This Philips GardenLink extension cable is made of high-quality materials. This ensures a solid and long-lasting product which is resistant to corrosion and stains in all weather conditions

## Extra safety with 24 V low voltage

Low-voltage (24 V) lights are safe to install without risk of electric shock – no professional electrician required.

# Specifications

## Design and finishing

- Colour: Black
- Material: PVC

## Environmental

• Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: No
- Fully weatherproof: Yes
- LED integrated: No
- Motion sensor: No
- Solar Energy: No
- Centrepiece: No

## Garden area

- Garden area: Garden and Patio

## Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Accessories
- Extra Features: Low Voltage, Water Resistant

## Product dimensions and weight

- Net weight: 0.4 kg
- Overall height: 20 mm
- Overall length: 10,000 mm
- Overall width: 20 mm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Fixture dimmable: No
- IP code: IP67 | Dust-tight and temporary immersion-proof
- Class of protection: NA

## Packaging dimensions and weight

- EAN/UPC – product: 8720169269354
- Net weight: 0.4 kg
- Gross weight: 0.45 kg
- Height: 13.7 cm
- Length: 10.2 cm
- Width: 10.2 cm



Issue date: 2025-11-01  
Version: 0.321

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)