

PHILIPS

Ceiling Light 21 W

Ceiling Lights

4000K

White



8720169296046



Hands-free light for safety and convenience

This Philips LED ceiling light can be easily turned on and off by the motion sensor. With a wide detection range, brighter light output and instant-on LED technology, you can be assured that your home space is well lit for security and visibility. Comfortable light that's easy on your eyes.

Easy to experience

- With its built-in automatic motion sensor, this luminaire switches on automatically when people walk by.

Premium quality

- EyeComfort – light that's easy on the eyes

Durability

- Long life span up to 15,000 hours

Highlights

Integrated motion sensor EyeComfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour

rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output and colour for more than a decade. Switch

to light that's easy on your eyes. Your eyes will thank you.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Colour: White
- Material: Metal, Plastic

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Number of switch cycles: 15,000
- Nominal lifetime: 15,000 h

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Warm-up time to 60% light: <2

Miscellaneous

- Type: Ceiling Lights
- EyeComfort: Yes

Other characteristics

- Lamp current: 183 mA
- Efficacy: 138 lm/W

Power consumption

- Power factor: 0.5

Product dimensions and weight

- Net weight: 0.6 kg
- Height: 7 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Diameter: 345 mm
- Total lumen output fixture: 2900
- Light colour: 4000
- Mains power: AC 220-240
- Fixture dimmable: No
- IP code: IP20
- Class of protection: Class I

Packaging dimensions and weight

- EAN/UPC - product: 8720169296046
- Net weight: 0.6 kg
- Gross weight: 0.89 kg
- Height: 38 cm
- Length: 8 cm
- Width: 38 cm



Issue date: 2025-05-01
Version: 0.140

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com