

PHILIPS

Alula Portable Light
1.2W

Outdoor luminaires

3000K

Black

RGB Colours; Solar; Water
Resistant



8720169296503



Light up your outdoor life

This Philips Alula solar portable light has 3-in-1 light setting modes. Simply knock or tap to enjoy two brightness level or RGB party mode.

Sustainable light solutions

- Long lifetime up to 15,000 hours

Advanced LED light

- High-quality LED light

Premium quality

- High quality material

Designed for outdoors

- IP44 – weatherproof

Highlights

Long lifetime up to 15,000 hours



Reliable high-quality LED light lasts up to 15,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, whilst having the perfect light ambiance in your home.

High quality material



This Philips outdoor lamp is made of high-quality materials with superior finishing. This ensures a solid and long-lasting product which is resistant to corrosion and stains in all weather conditions

IP44 – weatherproof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water – perfect for general outdoor use.

High-quality LED light



These LED lights use a unique technology developed by Philips. They turn on instantly and produce optimal light output that brings out the vivid colours in your garden.

Specifications

Design and finishing

- Colour: Black
- Material: Plastic

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- 5 year warranty on the LED module: Yes
- Adjustable spot head: No
- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: No
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: No
- Solar Energy: Yes
- Centrepiece: Yes

Light characteristics

- Beam angle: 120 degree(s)
- Colour rendering index (CRI): 80

Miscellaneous

- Especially designed for: Garden and Patio
- Style: Contemporary
- Type: Portable Lights
- EyeComfort: No
- Extra Features: RGB Colours, Solar, Water Resistant

Power consumption

- Wattage: 1.2 W

Product dimensions and weight

- Net weight: 0.362 kg
- Height: 15 cm
- Length: 13 cm
- Width: 12 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 h
- Total lumen output fixture: 80/20
- Light colour: 3000
- Mains power: 5, DC 4
- Fixture dimmable: No
- Energy class included light source: F
- IP code: IP44
- Class of protection: Class III
- Light source replaceable: No

Packaging dimensions and weight

- EAN/UPC – product: 8720169296503
- Net weight: 0.36 kg
- Gross weight: 0.44 kg
- Height: 12 cm
- Length: 14 cm
- Width: 15 cm



Issue date: 2025-04-19
Version: 0.152

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com