

# PHILIPS

## Rover Wall Light

Wall Lights

2700K

Brass

ClickFix; Water Resistant



8720169299511



## Stylish LED mirror light to brightly illuminate your bathroom

Philips offers mirror lights for all of your bathroom lighting needs. Our mirror lights are designed to perform in damp conditions, with protection against splashing water. Soft warm white LED light that's easy on your eyes. Install in four easy steps with the patented Philips ClickFix installation system. Made of robust materials selected for durability and visual appeal.

### Easy installation

- ClickFix easy mounting

### Match your interior style

- coordinated perfectly with other Philips bathroom lights

### Sustainable light solutions

- Long lifetime up to 25,000 hours

### Well-being in your bathroom with high-quality light

- Seeing well is essential in the bathroom

### High-quality light

- EyeComfort – light that's easy on your eyes

**Safety**

- Moisture resistance

**Durability**

- Long-lasting quality, even after years

# Highlights

## ClickFix easy mounting

Install in four easy steps with the patented Philips ClickFix installation system. Install your spot light easily and by yourself. Simply mount the bracket to the ceiling, connect the wires, then click and fix the light in one go.

## Extensive bathroom lighting portfolio

Philips offers mirror lights and ceiling spots for all of your bathroom lighting needs

## Long lifetime up to 25,000 hours



Reliable high-quality LED light lasts up to 25,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while having the perfect light ambience in your home.

## Seeing well is essential

Seeing well is essential for good results at the mirror, which is why each lamp features a high-quality light source for confident grooming. The bathroom lighting range uses the latest energy-saving technology for good quality light that provides plenty of illumination without being harsh.

## EyeComfort – light that's easy on your eyes



Poor-quality light can cause eye strain. With many people spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour rendition and dimming effects to ensure that they meet EyeComfort requirements. This Philips LED luminaire not only delivers comfortable light, but also stays that way for the duration of its lifespan, delivering consistent light quality, output and colour for more than a decade.

## Moisture resistance

Moisture resistance means you can confidently use this product in bathrooms, kitchens, balconies and other spaces where moisture may be a consideration.

## Durable and long lasting

Made of robust materials selected for durability and visual appeal. Built for long-lasting performance. Install it and forget it until the end of its long useful life – no hassling with replacements. High-quality materials have UV baking, high temperature and other endurance tests to ensure durability

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Colour: Brass
- Material: Metal, Plastic

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 25,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

**Extra feature/accessory incl.**

- click!FIX mounting: Yes
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

**Light characteristics**

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Warm-up time to 60% light: 2
- Luminous efficacy (rated) (nom.): 150 lm/W

**Miscellaneous**

- Especially designed for: Bathroom, Hall
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: ClickFix, Water Resistant

**Other characteristics**

- Lamp current: 75 mA

**Power consumption**

- Power factor: 0.5
- Power Consumption: 10

**Product dimensions and weight**

- Net weight: 0.683 kg
- Overall height: 50 mm
- Overall length: 630 mm
- Overall width: 50 mm

**Service**

- Warranty: 2 year(s)

**Technical specifications**

- Total lumen output fixture: 1500
- Light colour: 2700
- Mains power: AC 220-240
- Fixture dimmable: No
- Energy class included light source: D
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class I – Earthed
- Light source replaceable: No
- Number of light sources: 1

**Packaging dimensions and weight**

- EAN/UPC - product: 8720169299511
- Net weight: 0.63 kg
- Gross weight: 0.72 kg
- Height: 64 cm
- Length: 6.6 cm
- Width: 6.6 cm



Issue date: 2025-11-01  
Version: 0.295

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)