

# PHILIPS

## Niall Ceiling/Wall Spotlight 4x

Ceiling/Wall Spotlights

No bulb

Black & brass

ClickFix



8720169300132



## High-quality light, designed for any light effect

Include this practical Philips spotlight in your home. Choose your Philips GU10 LED bulb to go with your spot style and ensure a high-quality and long-lasting light.

### Ease of use

- Adjustable spot head
- No bulb included

### Easy installation

- ClickFix easy mounting

### Easy to experience

- Perfect for placement on wall or ceiling, the luminaire gives you the freedom to customise your look to match your interiors.

### Material and finishing

- High quality material

# Highlights

## Adjustable spot head



Direct the light where you want it most by simply adjusting, rotating or tilting the spot head of the lamp.

## No bulb included

This luminaire comes without a bulb, which enables you to choose the light output which is best suited to the room and your personal taste. Choosing a Philips LED bulb will ensure a high quality and long-lasting light output.

## ClickFix easy mounting



Install your spotlight easily and by yourself. Thanks to ClickFix, no extra pair of hands is needed. Simply mount the bracket to the ceiling, connect the wires, then click and fix the lamp in one go.

## Adaptable mounting for wall or ceiling High quality material



Durable and attractive material for an attractive and long-lasting investment.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Colour: Black & Brass
- Material: Metal

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: Yes
- click!FIX mounting: Yes
- Dimmable with remote control: No
- LED integrated: No
- Remote control included: No

## Light characteristics

- Warm-up time to 60% light: <2

## Miscellaneous

- Especially designed for: Bedroom, Dining Room, Garage, Hallway, Kitchen, Living Room
- Style: Contemporary
- Type: Ceiling/Wall Spotlights
- EyeComfort: No
- Extra Features: ClickFix

## Other characteristics

- Lamp current: 200 mA

## Product dimensions and weight

- Net weight: 0.695 kg
- Height: 11 cm
- Length: 69 cm
- Width: 13 cm

## Service

- Warranty: 2 year(s)

#### Technical specifications

- Mains power: AC 220-240
- Fixture dimmable: No
- Fitting/cap: GU10
- Maximum wattage replacement bulb: 5
- IP code: IP20
- Class of protection: Class I
- Number of light sources: 4

#### Packaging dimensions and weight

- EAN/UPC – product: 8720169300132
- Net weight: 0.7 kg
- Gross weight: 0.88 kg
- Height: 70.3 cm
- Length: 11 cm
- Width: 12 cm



Issue date: 2025-06-13  
Version: 0.218

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)