

PHILIPS

Ceiling Light 10 W

Ultra Efficient

4000K

Black

Dual brightness

8720169301115



Comfortable LED light that's easy on your eyes

Brightness change: With Philips SceneSwitch LED ceiling light, you can enjoy 3 brightness settings to suit whatever you're doing. Comfortable light that's easy on your eyes. All you need is your existing switch. Colour change: change your room ambiance to suit whatever you're doing. With the Philips SceneSwitch LED ceiling light, you can easily change the setting from bright light, to natural light and to a cosy warm glow. Comfortable light that's easy on your eyes. No dimmer or additional installation required. All you need is your existing switch.

Sustainable light solutions

- High quality LED light

Designed for your living room and bedroom

- Create a stylish and welcoming atmosphere

Light effect

- Bright light with uniform distribution

Highlights

High quality LED light



The LED technology integrated into this Philips lamp is a unique solution developed by Philips. It turns on

instantly, enables an optimal light output and brings out vivid colours in your home.

Create a stylish atmosphere



This light is designed around the latest tastes, trends and lifestyles to blend effortlessly into your décor and define the localised ambience you have always desired.

Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Colour: Black
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 51 year(s)
- Number of switch cycles: 25,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bedroom, Dining Room, Living Room
- Style: Modern
- Type: Ceiling Lights
- EyeComfort: Yes
- LED innovations: EyeComfort, UltraEfficient
- Extra Features: Dual Brightness

Other characteristics

- Lamp current: 95 mA
- Efficacy: 195 lm/W

Power consumption

- Power factor: 0.5

Product dimensions and weight

- Net weight: 0.66 kg
- Height: 5 cm

Service

- Warranty: 5 year(s)

Technical specifications

- Lifetime up to: 50,000 h
- Diameter: 320 mm
- Total lumen output fixture: 1950
- Light colour: 4000
- Mains power: AC 220-240
- Fixture dimmable: Step Dim – Do not use with dimmer
- LED: Yes
- IP code: IP20
- Class of protection: Class II



Issue date: 2025-04-19
Version: 0.213

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com