

PHILIPS

Spot 60 W R7S R7S

LED

3000K

950 lm

15000 h



8720169301894



Bright LED lighting with excellent light quality

This innovative Linear LED is the perfect replacement for halogen R7S bulbs, while far surpassing them in terms of energy efficiency.

High-quality light

- Cool, energising light

Choose a simple replacement for your old lamps

- Similar shape and size as halogen linears

Choose for a sustainable solution

- Saves up to 80% energy

Highlights

3500K [LED Lamps]



This bulb has a colour temperature of 3,500 K providing you with a cool, energising light, perfect for creating an inviting ambiance to host friends or wind down with a book.

Replaces linear halogens



With its beautifully shaped design and familiar dimensions, this standard modern lighting, LED linear is the perfect sustainable replacement for traditional halogen linears.

Saves up to 80% energy



Enjoy the energy savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

Specifications

General

- Suitable for accent lighting: No

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional reflector
- Socket: R7s
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Clear plastic

Durability

- Number of switch cycles: 50,000
- Ambient temperature range: -20 to +45 °C
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Guarantee

- Warranty period: 2 years

Light characteristics

- Beam angle: 300 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 3000 K
- Nominal luminous flux: 950 lm
- Warm-up time to 60% light: 0.5 s
- Correlated Colour Temperature (Nom): 3000
- Luminous Flux: 950 lm
- Stroboscopic effect: 0.4
- Luminous efficacy (rated) (nom.): 135

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

Other characteristics

- CE mark: Yes
- EU RoHS compliant: Yes

Packaging information

- EAN: 8720169301894
- EOC: 872016930189400
- Product title: LED 60W R7S 78mm
WH RF ND SRT4

Power

- Power Factor (Fraction): 0.5

Power consumption

- Power factor: 0.5
- Voltage: AC 220-240 V
- Wattage equivalent: 60
- Energy efficiency label (EEL): D
- Power: 7
- Energy consumption kWh/1,000
hours: 7

Product dimensions and weight

- Overall height: 78 mm
- Overall length: 78 mm
- Overall width: 28 mm

Technical specifications

- Frequency: 50-60
- Bulb technology: LED
- EPREL Registration Number: 1932586
- Flux measurement reference: Sphere
- Dimmable: No
- Flickering value (PstLM): 1
- Cap base: R7s
- Can it be used in closed luminaires:
No

What's supported

- Compatible operating systems: Not
applicable

Packaging dimensions and weight

- EAN/UPC - product: 8720169301894
- Net weight: 0.04 kg
- Gross weight: 0.06 kg
- Height: 12.7 cm
- Length: 3 cm
- Width: 6.3 cm



Issue date: 2026-04-04
Version: 0.264

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com