

# PHILIPS

Globe 75W G95 E27

Smart LED

Tunable white smart bulb

Up to 1055 lumens

Easy plug and play

Control with app or voice



8720169303058



## Smart lighting for your daily living

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: G95
- Socket: E27
- Type of glass: Frosted
- Lamp Finish: Frosted
- Dimmable: Yes

## Lamp dimensions

- Weight: 0.09 kg

## Design and finishing

- Colour: White
- Material: Plastic

## Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000
- Nominal lifetime: 25,000

## Extra feature/accessory incl.

- Adjustable spot head: No
- Choose your colour: Yes
- Fully weatherproof: No
- LED integrated: Yes
- Solar Energy: No
- Warm glow dimmable light: No

## Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI):  $\geq 80$
- Colour temperature: 2200–6500 K
- Light Colour Category: Tunable white
- Nominal luminous flux: 1055 lm
- Starting time:  $< 0.5$  s
- Warm-up time to 60% light: Instant full light
- Luminous efficacy (rated) (nom.): 95

## Miscellaneous

- Especially designed for: Bedroom, Dining Room, Living Room, Children's room
- EyeComfort: Yes

## Other characteristics

- Lamp current: 75 mA

## Packaging information

- EAN: 8720169303058
- EOC: 872016930305800
- Product title: PHI WFB 75W G95 E27 827-65 TW 1PF/6

## Power consumption

- Power factor: 0.5
- Voltage: AC 220–240 V
- Energy efficiency label (EEL): F
- Power: 11 W
- Energy consumption kWh/1,000 hours: 11

## Product dimensions and weight

- Overall height: 139 mm
- Overall length: 139 mm
- Overall width: 95 mm

## Rated values

- Rated lifetime: 25,000
- Rated luminous flux: 1055 lm
- Rated power: 11 W

## Service

- Warranty: 2 year(s)

## Technical specifications

- Frequency: 50–60
- Diameter: 95 mm
- Bulb technology: LED
- Light colour: Tunable white light
- IP code: IP20 | Finger-protected
- EPREL Registration Number: 1877821
- Flux measurement reference: Sphere

## The bulb

- Diameter: 95 mm
- Software upgradable: Yes

### What's supported

- Compatible with Effects feature: Yes
- WiFi: 802.11b/g/n
- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999
- Compatible operating systems: iOS, Android
- Communication protocol: Bluetooth, WiFi (2.4GHz)
- Compatibility with third-party systems: Alexa, Google Home,

- Homey, IFTTT, Matter, Samsung SmartThings, Siri Shortcuts
- Matter functionality: Via third-party hubs (Wi-Fi)

### Packaging dimensions and weight

- EAN/UPC - product: 8720169303058
- Net weight: 0.1 kg
- Gross weight: 0.21 kg
- Height: 18.5 cm
- Length: 10.5 cm
- Width: 10.5 cm



Issue date: 2026-04-22  
Version: 0.124

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)