

PHILIPS

Pomeron Recessed
light

Recessed Lights

4000K

Black

SceneSwitch



8720169304178



One fixture. Your switch. Three light settings.

Change your room ambiance to suit whatever you're doing. With the Philips SceneSwitch LED downlight, you can easily change the setting from bright light, to natural light and to a cosy warm glow. Comfortable light that's easy on your eyes. No dimmer or additional installation required. All you need is your existing switch.

Sustainable light solutions

- High quality LED light

Light effect

- Bright and focused beam

Control

- 3-step dimming

Durability

- Long life span up to 15,000 hours

Highlights

High quality LED light



The LED technology integrated into this Philips lamp is a unique solution developed by Philips. It turns on instantly, enables an optimal light output and brings out vivid colours in your home.

Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

3-step dimming

Choose between three levels of brightness to match your mood and activity.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

Design and finishing

- Colour: Black
- Material: Metal, Plastic

Durability

- Number of switch cycles: 7,500
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 30 degree(s)
- Colour consistency: 5 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Warm-up time to 60% light: 2
- Luminous efficacy (rated) (nom.): 62 lm/W

Miscellaneous

- Especially designed for: Bedroom, Dining Room, Garage, Hall, Office, Kitchen, Living Room
- Style: Modern
- Type: Recessed Lights
- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: SceneSwitch

Other characteristics

- Lamp current: 44 mA

Power consumption

- Power factor: 0.5
- Power Consumption: 5

Product dimensions and weight

- Net weight: 0.114 kg
- Recessed distance: 60 mm
- Overall height: 60 mm
- Recessed ceiling cutout: 7.0 cm x 7.0 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Diameter: 90 mm
- Total lumen output fixture: 350
- Light colour: 4000
- Mains power: AC 220-240
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated
- Number of light sources: 1

Packaging dimensions and weight

- EAN/UPC – product: 8720169304178
- Net weight: 0.11 kg
- Gross weight: 0.14 kg
- Height: 8.7 cm
- Length: 9.5 cm
- Width: 9.5 cm



Issue date: 2025-10-11
Version: 0.196

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com