

# PHILIPS

Sparkle Recessed  
Light

Recessed Lights

2700K

Black

Dimmable



8720169304215



## Comfortable LED light that's easy on your eyes

Create the perfect mood with Philips LED Dimmable recessed spots, you can easily dim your lights from everyday bright light to cosy tones.

### Sustainable light solutions

- High quality LED light

### Light effect

- Bright and focused beam

### Control

- Dimmable

### Durability

- Long life span of up to 20,000 hours

# Highlights

## High quality LED light



The LED technology integrated into this Philips lamp is a unique solution developed by Philips. It turns on instantly, enables an optimal light output and brings out vivid colours in your home.

## Dimmable

Allows you to change the mood by reducing LED brightness levels, from bright white light to a cosy glow – just like traditional lamps.

## Long life span of up to 20,000 hours

Philips LED technology extends your product's lifetime up to 20,000 hours.

## Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Colour: Black
- Material: Metal, Plastic

## Durability

- Number of switch cycles: 10,000
- Nominal lifetime: 20,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: Adjustable – rise and fall
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 36
- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Warm-up time to 60% light: 2
- Luminous efficacy (rated) (nom.): 64

## Miscellaneous

- Especially designed for: Kitchen, Bedroom, Dining Room, Garage, Living Room, Office, Hall
- Style: Modern
- Type: Recessed Lights
- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Dimmable

## Other characteristics

- Lamp current: 29 mA

## Power consumption

- Power factor: 0.8
- Power: 5

## Product dimensions and weight

- Net weight: 0.118 kg
- Recessed distance: 20 mm
- Overall height: 60 mm
- Recessed ceiling cutout: 7.0 cm x 7.0 cm

## Service

- Warranty: 2 year(s)

### Technical specifications

- Diameter: 85 mm
- Total lumen output fixture: 350
- Bulb technology: LED
- Light colour: Warm white light
- Mains power: AC 220-240
- Fixture dimmable: Yes
- IP code: IP20
- Class of protection: Class II – Double Insulated
- Number of light sources: 1

### The bulb

- Software upgradable: No

### What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

### Packaging dimensions and weight

- EAN/UPC – product: 8720169304215
- Net weight: 0.35 kg
- Gross weight: 0.42 kg
- Height: 9.2 cm
- Length: 10.7 cm
- Width: 18.9 cm



Issue date: 2026-05-30  
Version: 0.204

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)