

PHILIPS

UltraEfficient Spot
50 W PAR16 GU10

Ultra Efficient

3000K

375 lm

50000 h

Dimming



8720169307889



Ultra-efficient spot, sustainable lamp with dimmable function

Philips LED spots provide a focused bright beam, an exceptionally long life, and saving up to 47% energy. This spot is the perfect long-lasting replacement for 50 W spots with a GU5.3 cap.

Designed to last longer and save more energy

- Everyday switch on, save energy

The right choice for high-quality accent light

- 5-year warranty

The right replacement for your old lamps

- Similar shape and size to standard halogen lamp

Dimmable (LED lamps)

- Dimmable (LED lamps)

Highlights

Everyday switch on, save energy



Our UltraEfficient LEDs are at least 40% more energy-efficient than standard Philips LEDs, saving you energy every day

5-year warranty

Enjoy long-lasting, high-quality light with our generous 5-year warranty

Similar shape and size to standard halogen lamp



With its beautifully shaped design and familiar dimensions, this is a modern lighting energy-saving, standard, LED lamp. The perfect sustainable replacement for traditional standard halogen lamps.

Dimmable (LED lamps)



This lamp can be used with most dimmers to create your desired ambience with smooth dimming. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this lamp.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Lamp Finish: Clear
- Dimmable: Yes
- Bulb material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 50,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Beam angle: 36
- Colour rendering index (CRI): 80
- Colour temperature: 3000 K
- Nominal luminous flux: 375 lm
- Luminous efficacy (rated) (nom.): 178

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort, UltraEfficient

Packaging information

- EAN: 8720169307889
- EOC: 872016930788900
- Product title: LEDClassic 50W GU10 WH 36D DIM UE SRT4

Power consumption

- Power factor: 0.7
- Voltage: AC 220-240 V
- Wattage equivalent: 50
- Power: 2.1
- Energy consumption kWh/1,000 hours: 3

Product dimensions and weight

- Overall height: 54 mm
- Overall length: 54 mm
- Overall width: 50 mm

Rated values

- Rated peak intensity: 650 cd

Technical specifications

- Frequency: 50-60
- Bulb technology: LED
- Can it be used in closed luminaires:
Yes

Packaging dimensions and weight

- EAN/UPC - product: 8720169307889
- Net weight: 0.22 kg
- Gross weight: 0.29 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 6.3 cm



Issue date: 2026-03-31
Version: 0.122

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com