

# PHILIPS

GU10 Spot 50 W  
PAR16

Ultra Efficient

4000K

375 lm

50000 h

Dimming



8720169307902



## UltraEfficient LED, our most energy-efficient LED lamp yet

Philips UltraEfficient LED lamps provide beautiful, warm white light, offer an exceptionally long lifetime of 50,000 hours, and deliver immediate and significant energy savings. Reduce the frequency of lamp replacements and enjoy light that's easy on the eyes with our trusted EyeComfort design.

### **Designed to last longer and save more energy**

- Everyday switch on, save energy

### **The right choice for high-quality accent light**

- 5-year warranty

### **The right replacement for your old lamps**

- Similar shape and size to standard halogen lamp

### **Dimmable (LED lamps)**

- Dimmable (LED lamps)

# Highlights

## Everyday switch on, save energy



Our UltraEfficient LEDs are at least 40% more energy-efficient than standard Philips LEDs, saving you energy every day

## 5-year warranty

Enjoy long-lasting, high-quality light with our generous 5-year warranty

## Similar shape and size to standard halogen lamp



With its beautifully shaped design and familiar dimensions, this is a modern lighting energy-saving, standard, LED lamp. The perfect sustainable replacement for traditional standard halogen lamps.

## Dimmable (LED lamps)



This lamp can be used with most dimmers to create your desired ambience with smooth dimming. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this lamp.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Lamp Finish: Clear
- Dimmable: Yes
- Bulb material: Glass

## Lamp dimensions

- Height: 5.4 cm
- Width: 5 cm

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 50,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 36 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Nominal luminous flux: 375 lm

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort, UltraEfficient

## Other characteristics

- Efficacy: 178 lm/W

## Packaging information

- EAN: 8720169307902
- EOC: 872016930790200
- Product title: LEDClassic 50W GU10 CW 36D DIM UE SRT4

## Power consumption

- Power factor: 0.7
- Voltage: AC 220-240 V
- Wattage: 2.1 W
- Wattage equivalent: 50 W
- Energy consumption kWh/1,000 hours: 3

**Product dimensions and weight**

- Length: 5.4 cm

**Rated values**

- Rated peak intensity: 650 cd

**Technical specifications**

- Frequency: 50-60 Hz

**Packaging dimensions and weight**

- EAN/UPC – product: 8720169307902
- Net weight: 0.22 kg
- Gross weight: 0.29 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 6.3 cm



Issue date: 2025-05-24  
Version: 0.131

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)