

PHILIPS

Bulb 40 W A60 E27

LED

6500K

470 lm

15000 h



8720169324077



Bright LED lighting with excellent light quality

Philips LED light bulbs provide a cool white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your matted traditional bulbs.

High-quality light

- Designed for the comfort of your eyes

Choose a simple replacement for your old lamps

- Similar shape and size as standard incandescent bulbs

Choose for a sustainable solution

- Long-life bulbs – Last up to 15 years

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Replaces standard incandescents



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Lamp Finish: Frosted
- Dimmable: No
- Bulb material: Plastic

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 150 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 6500 K
- Nominal luminous flux: 470 lm
- Luminous efficacy (rated) (nom.): 111

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

Packaging information

- EAN: 8720169324077
- EOC: 872016932407700
- Product title: LED 40W A60 E27 CDL FR ND 1SRT4

Power consumption

- Power factor: 0.48
- Voltage: AC 220-240 V
- Wattage equivalent: 40 W
- Energy efficiency label (EEL): E
- Power: 4.2 W
- Energy consumption kWh/1,000 hours: 5

Product dimensions and weight

- Overall height: 107 mm
- Overall length: 107 mm
- Overall width: 60 mm

Technical specifications

- Frequency: 50-60
- EPREL Registration Number: 1930256
- Can it be used in closed luminaires:
No

Packaging dimensions and weight

- EAN/UPC - product: 8720169324077
- Net weight: 0.02 kg
- Gross weight: 0.04 kg
- Height: 14.6 cm
- Length: 6.5 cm
- Width: 6.3 cm



Issue date: 2026-03-07
Version: 0.203

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com