

PHILIPS

Filament Candle Clear
40 W B35 E14 x2

Ultra Efficient


2700K

485 lm

50000 h



8720169325098



UltraEfficient lamp, our most energy-efficient LED bulbs

Philips UltraEfficient LED lamps provide beautiful light, offer an exceptionally long lifetime of 50,000 hours, and deliver immediate and significant energy savings. Reduce the frequency of lamp replacements and enjoy light that's easy on the eyes with our trusted EyeComfort design.

High-quality light

- Designed for the comfort of your eyes

Designed to last longer and save more energy

- Everyday switch on, save energy
- Long life bulb – Lasts up to 50 years

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Everyday switch on, save energy



Our UltraEfficient LEDs are at least 50% more energy-efficient than standard Philips LEDs, saving you energy every day

Long life bulb – Lasts up to 50 years



Avoid the hassle of frequent light bulb replacements. With a lifetime of up to 50,000 hours, our UltraEfficient LEDs last 3.5 times longer than standard Philips LEDs, so you can enjoy a perfect lighting solution for more than 50 years.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional candle
- Socket: E14
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

Lamp dimensions

- Height: 9.7 cm
- Width: 3.5 cm

Durability

- Number of switch cycles: 500,000
- Nominal lifetime: 50,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 300 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 485 lm

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort, UltraEfficient

Other characteristics

- Efficacy: 210 lm/W

Packaging information

- EAN: 8720169325098
- EOC: 872016932509800
- Product title: LED CLA 40W B35 E14 2700K CL UE 2PF/SRT

Power consumption

- Power factor: 0.4
- Voltage: AC 220–240 V
- Wattage equivalent: 40 W
- Energy efficiency label (EEL): A
- Power Consumption: 2.3 W
- Energy consumption kWh/1,000 hours: 3

Product dimensions and weight

- Length: 9.7 cm

Technical specifications

- Frequency: 50-60 Hz
- EPREL Registration Number: 1881210

Packaging dimensions and weight

- EAN/UPC – product: 8720169325098
- Net weight: 0.03 kg
- Gross weight: 0.07 kg
- Height: 14.6 cm
- Length: 4.6 cm
- Width: 8.5 cm



Issue date: 2025-06-13
Version: 0.222

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com