

# PHILIPS

Kinno Pedestal/Pathway  
Lights 25W E27 No-bulb

Outdoor luminaires

No bulb

Black

Water Resistant

8720169351431



## Enjoy a beautiful garden

This Philips Kinno outdoor light is designed around the latest trends and lifestyles to define the ambience you have always desired.

### **Ease of use**

- No bulb included

### **Bring design into your garden**

- Stylish contemporary designs for your garden
- Choose for outdoor pedestal lights

### **Premium quality**

- High quality material

### **Designed for outdoors**

- IP44 – weatherproof

# Highlights

## No bulb included

This luminaire comes without a bulb, which enables you to choose the light output which is best suited to the room and your personal taste. Choosing a Philips LED bulb will ensure a high quality and long-lasting light output.

## Stylish contemporary designs for your garden

These contemporary designs by Philips are stylish but understated, beautiful by day or night without overwhelming your garden or terrace. There is a full range of lights to choose from, so there is bound to be one to match your outside space and taste.

## Choose for outdoor pedestal lights

Make the most of your outdoor space with this pedestal light, perfect to light your garden, the edge of your terrace or to accentuate driveways and paths.

## High quality material



This Philips outdoor lamp is made of high-quality materials with superior finishing. This ensures a solid and long-lasting product which is resistant to corrosion and stains in all weather conditions.

## IP44 – weatherproof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water – perfect for general outdoor use.

# Specifications

## Design and finishing

- Colour: Black
- Material: Aluminium

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- 5 year warranty on the LED module: Yes
- Adjustable spot head: No
- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: No
- Fully weatherproof: Yes
- LED integrated: No
- Motion sensor: No
- Solar Energy: No
- Centrepiece: No

## Miscellaneous

- Especially designed for: Garden and Patio
- Style: Contemporary
- Type: Pedestal/Pathway Lights
- EyeComfort: No
- Extra Features: Water Resistant

#### Product dimensions and weight

- Net weight: 1.1 kg
- Height: 39 cm
- Length: 17 cm
- Width: 17 cm

#### Service

- Warranty: 2 year(s)

#### Technical specifications

- Mains power: AC 220-240
- Fixture dimmable: No
- Fitting/cap: E27
- Maximum wattage replacement bulb:  
25 W
- IP code: IP44
- Class of protection: Class I
- Light source replaceable: Yes

#### Packaging dimensions and weight

- EAN/UPC – product: 8720169351431
- Net weight: 1.1 kg
- Gross weight: 1.28 kg
- Height: 41.5 cm
- Length: 20 cm
- Width: 20 cm



Issue date: 2025-04-19  
Version: 0.273

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)