

PHILIPS

Filament clear 60 W
A60 B22

Smart LED

Tunable white smart bulb

Up to 903 lumens

Easy plug and play

Control with app or voice

8720169353718



Smart lighting for your daily living

The Philips A60 ultra efficient smart bulb is our most energy-efficient smart bulb. This A-class rated smart light bulb that consumes 40% less energy than standard LED and connected LED light bulbs. Convenient wireless dimming and easy Wi-Fi based make controlling these lights a breeze—no need to install an expensive dimmer. If you're interested in making the transition to smart lighting, this is a great place to start: best-in-class energy efficiency out of the box, with additional smart features that you can use whenever you like

Easy setup

- Easy plug and play

Smart control

- Control from anywhere with your smartphone

Smart features

- Preset wellbeing features
- Automate your device with schedules
- Energy monitoring

Light modes

- Tunable warm to cool white and preset modes


8720169353718

Form factor

- Multi-application and simple installation

Highlights

Easy plug and play



WiZ works with your existing Wi-Fi router, no additional gateway is needed. Simply plug in your new light, download the WiZ app and you're ready to go!

Control from anywhere




Control your WiZ lights wherever you are with your smartphone. No need to worry if you've left your lights on before leaving home. The WiZ app is available for iOS and Android.

Preset wellbeing features



Use the preset wellbeing features in the WiZ app to and enjoy the lighting pattern best suited for your circadian rhythm through the day. WiZ will provides you bright daylight when you need to get energised and focus, and transition smoothly to soft warm white to help you relax and sleep better.

Automate your device with schedules



Schedule your device to turn on/off to fit your daily routine and save energy.

Energy monitoring



The WiZ app keeps records of the energy consumption of your lights. View your weekly or daily report and plan your lighting wisely for optimised energy consumption at home.

Tunable warm to cool white and preset modes



Choose from a wide range of energising cool white to soft warm white, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.

Multi-application and simple installation



Simply stick to any surface you like – window displays, tray ceilings, work stations and under cabinets. Brightening up and adding accent to your furniture.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: A60
- Socket: B22
- Type of glass: Clear
- Lamp Finish: Clear
- Dimmable: Yes

Lamp dimensions

- Weight: 0.055 kg

Durability

- Average life (at 2.7 hrs/day): 51 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000
- Nominal lifetime: 50,000

Extra feature/accessory incl.

- LED integrated: Yes
- Solar Energy: No
- Warm glow dimmable light: No

Light characteristics

- Beam angle: 300
- Colour consistency: 6 SDCM
- Colour rendering index (CRI): ≥ 80
- Colour temperature: 2700–4000 K
- Light Colour Category: Tunable white
- Nominal luminous flux: 903 lm
- Starting time: < 0.5 s
- Warm-up time to 60% light: Instant full light
- Luminous efficacy (rated) (nom.): 210

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 42 mA

Packaging information

- EAN: 8720169353718
- EOC: 872016935371800
- Product title: PHI WFB 60W A60 B22 827-40 TW EELA 1PF

Power consumption

- Power factor: 0.48
- Voltage: AC 220–240 V
- Energy efficiency label (EEL): A
- Power: 4.3 W
- Energy consumption kWh/1,000 hours: 5

Product dimensions and weight

- Overall height: 126 mm
- Overall length: 126 mm
- Overall width: 60 mm

Rated values

- Rated lifetime: 50,000
- Rated luminous flux: 903 lm
- Rated power: 4.3 W

Technical specifications

- Frequency: 50–60
- Bulb technology: LED
- EPREL Registration Number: 2004761
- Flux measurement reference: Sphere

The bulb

- Software upgradable: Yes

What's supported

- Compatible with Effects feature: Yes
- WiFi: 802.11b/g/n
- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999
- Compatible operating systems: iOS, Android
- Communication protocol: Bluetooth, WiFi (2.4GHz)
- Compatibility with third-party systems: Alexa, Google Home, Homey, IFTTT, Matter, Samsung SmartThings, Siri Shortcuts
- Matter functionality: Via third-party hubs (Wi-Fi)

Packaging dimensions and weight

- EAN/UPC - product: 8720169353718
- Net weight: 0.06 kg
- Gross weight: 0.09 kg
- Height: 18.5 cm
- Length: 8.5 cm
- Width: 8.5 cm



Issue date: 2026-04-22
Version: 0.106

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com