

# PHILIPS

Filament bulb ST64  
27K


Ultra-efficient Solar

2700K

Glass

Solar

8720169361980



## Truly long-lasting with replaceable lamp and batteries

Philips solar bulb designed specially for UltraEfficient outdoor luminaires.

### **Sustainable light solutions**

- Long lifetime up to 15,000 hours

### **High-quality light**

- Warm white light 2,700 K

# Highlights


## Long lifetime up to 15,000 hours



Reliable high-quality LED light lasts up to 15,000 hours. You can rest easy

knowing that you won't have to worry about maintenance for years, while enjoying the perfect garden light every night.

## Warm white light 2,700 K



Did you know that different shades of white light are identified by different colour temperatures, measured in Kelvin (K)? Lower colour temperatures produce a warm, cosy white light, while higher colour temperatures produce a cool, more energising white light. This luminaire produces warm, relaxing light at 2,700 K.

# Specifications

## Design and finishing

- Colour: Glass
- Material: Glass

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- 5 year warranty on the LED module: Yes
- Adjustable spot head: No
- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: No
- Fully weatherproof: No
- LED integrated: Yes
- Motion sensor: No
- Solar Energy: No
- Centrepiece: No

## Light characteristics

- Colour rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Garden and Patio
- Style: Contemporary
- Type: Accessories
- LED innovations: UltraEfficient
- Extra Features: Solar

## Power consumption

- Wattage: 2.5 W

## Product dimensions and weight

- Net weight: 0.04 kg
- Height: 13 cm
- Length: 6 cm
- Width: 6 cm

## Service

- Warranty: 2 year(s)

#### Technical specifications

- Lifetime up to: 15,000 h
- Total lumen output fixture: 500
- Light colour: 2700
- Mains power: DC 27
- Fixture dimmable: No
- Energy class included light source: B
- IP code: IP20
- Class of protection: Class III

- Number of light sources: 1

#### Packaging dimensions and weight

- EAN/UPC – product: 8720169361980
- Net weight: 0.04 kg
- Gross weight: 0.1 kg
- Height: 15.5 cm
- Length: 8.5 cm
- Width: 8.5 cm



Issue date: 2025-04-19  
Version: 0.245

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)