

PHILIPS

Filament bulb ST64
40K


Ultra-efficient Solar

4000K

Glass

Solar

8720169362000



Truly long-lasting with
replaceable lamp and
batteries

Philips solar bulb designed specially for UltraEfficient outdoor
luminaires.

Sustainable light solutions

- Long lifetime up to 15,000 hours

High-quality light

- Cool white light 4,000 K

Highlights

Long lifetime up to 15,000 hours



Reliable high-quality LED light lasts up to 15,000 hours. You can rest easy

knowing that you won't have to worry about maintenance for years, while enjoying the perfect garden light every night.

Cool white light 4,000 K



Did you know that different shades of white light are identified by different colour temperatures, measured in Kelvin (K)? Lower colour temperatures produce a warm, cosy white light, while higher colour temperatures produce a cool, more energising white light. This luminaire produces cool white light at 4,000 K.

Specifications

Design and finishing

- Colour: Transparent
- Material: Glass

Durability

- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: No
- Fully weatherproof: No
- LED integrated: Yes
- Motion sensor: No
- Solar Energy: No
- Centrepiece: No

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 4000 K

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Accessories
- LED innovations: UltraEfficient
- Extra Features: Solar

Power consumption

- Power: 2.5

Product dimensions and weight

- Net weight: 0.04 kg
- Overall height: 130 mm
- Overall length: 60 mm
- Overall width: 60 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Total lumen output fixture: 500
- Light colour: Cool white light
- Mains power: DC 27
- Fixture dimmable: No
- IP code: IP20 | Finger-protected
- Class of protection: Class III – Safe Extra Low Voltage
- Number of light sources: 1

Packaging dimensions and weight

- EAN/UPC – product: 8720169362000
- Net weight: 0.04 kg
- Gross weight: 0.1 kg
- Height: 15.5 cm
- Length: 8.5 cm
- Width: 8.5 cm



Issue date: 2025-12-31
Version: 0.265

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com