

PHILIPS

Ashlyn Ground
Spots/Spikes 1.4 W

Outdoor Solar

2700K

Black

Dusk to Dawn; Solar; Water
Resistant



8720169362246



Long-lasting solar- powered garden light for all seasons

Philips Ashlyn is a reliable solar light that lasts for a longer time, reduces energy consumption and supports sustainability.

Ease of use

- Adjustable light direction

Easy installation

- No wiring required

Sustainable light solutions

- Long lifetime up to 25,000 hours

Premium quality

- High quality material

Designed for outdoors

- IP44 – weatherproof

High-quality light

- Warm white light 2,700 K

Highlights

Adjustable light direction

A unique rotatable panel lets you easily direct light wherever you need it. Create the perfect light for all your outdoor activities – whether you're having dinner with family and friends on your patio or relaxing with a good book in your back garden.

No wiring required



This light is powered entirely by solar energy. No wiring is needed, making these lights easy to position and reposition anywhere in your garden or other outdoor area.

Long lifetime up to 25,000 hours



Reliable high-quality LED light lasts up to 25,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while having the perfect light ambience in your home.

High quality material




This Philips outdoor lamp is made of high-quality materials with superior finishing. This ensures a solid and long-lasting product which is resistant to corrosion and stains in all weather conditions

IP44 – weatherproof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water – perfect for general outdoor use.

Warm white light 2,700 K



Did you know that different shades of white light are identified by different colour temperatures, measured in Kelvin (K)? Lower colour temperatures produce a warm, cosy white light, while higher colour temperatures produce a cool, more energising white light. This luminaire produces warm, relaxing light at 2,700 K.

Specifications

Design and finishing

- Colour: Black
- Material: Plastic

Durability

- Nominal lifetime: 25,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Adjustable – rise and fall
- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: Yes
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: No
- Solar Energy: Yes
- Centrepiece: No

Light characteristics

- Beam angle: 120
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Ground Spots/Spikes
- EyeComfort: No
- Extra Features: Dusk to dawn, Solar, Water Resistant

Power consumption

- Power: 1.4

Product dimensions and weight

- Net weight: 0.35 kg
- Overall height: 350 mm
- Overall length: 130 mm
- Overall width: 190 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Total lumen output fixture: 150
- Bulb technology: LED
- Light colour: Warm white light
- Mains power: DC 4
- Fixture dimmable: No
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class III – Safe Extra Low Voltage
- Light source replaceable: No

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC – product: 8720169362246
- Net weight: 0.35 kg
- Gross weight: 0.5 kg
- Height: 21.5 cm
- Length: 15 cm
- Width: 11.5 cm



Issue date: 2026-04-15
Version: 0.254

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com