

PHILIPS

Lois Wall Lights
30W

Outdoor luminaires

5000 K

Black

Water Resistant



8720169365124



Powerful light, long-lasting quality

Philips Lois outdoor floodlights provide powerful light with durable design, to provide long-lasting brightness for your garden.

Ease of use

- A full range of available applications

Sustainable light solutions

- Long lifetime up to 15,000 hours

Premium quality

- High-quality aluminium and real glass

Designed for outdoors

- IP44 – weatherproof

High-quality light

- High light output

Highlights

A full range of available applications

Ideal outdoor lighting for a garden, terrace, pathway or balcony, Philips outdoor wall, post, pedestal and ceiling lights create a cosy, relaxing atmosphere when the sun goes down, as well as providing the reassurance of being able to see safely after dark.

Long lifetime up to 15,000 hours



Reliable high-quality LED light lasts up to 15,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while enjoying the perfect garden light every night.

High-quality aluminium and real glass



This Philips light is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high quality die-cast aluminium and real glass.

IP44 – weatherproof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water – perfect for general outdoor use.

High light output

Brighten up your home with high-quality light

Specifications

Design and finishing

- Colour: Black
- Material: Aluminium

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- 5 year warranty on the LED module: Yes
- Adjustable spot head: Yes
- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: No
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: No
- Solar Energy: No
- Centrepiece: No

Light characteristics

- Colour rendering index (CRI): 80

Miscellaneous

- Especially designed for: Garden and Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Water Resistant

Power consumption

- Wattage: 30 W

Product dimensions and weight

- Net weight: 0.355 kg
- Height: 15 cm
- Length: 16 cm
- Width: 3 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 15,000 h
- Total lumen output fixture: 3200
- Light colour: 5000
- Mains power: AC 220-240
- Fixture dimmable: No
- Energy class included light source: F
- IP code: IP65
- Class of protection: Class I
- Light source replaceable: No
- Number of light sources: 1

Packaging dimensions and weight

- EAN/UPC – product: 8720169365124
- Net weight: 0.35 kg
- Gross weight: 0.37 kg
- Height: 16.6 cm
- Length: 3.7 cm
- Width: 14.2 cm



Issue date: 2025-04-19
Version: 0.196

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com