

# PHILIPS

Lois Wall Lights 14W

Ultra Efficient

3000K

Anthracite

Water Resistant



8720169365384



## Our most energy-efficient LED lights yet

Philips Lois Ultra Efficient outdoor floodlights use groundbreaking new technology to cut carbon emissions, reduce material waste and lower energy usage. With an amazing lifetime of 50,000 hours, these lights last more than twice as long as Philips LED outdoor equivalents, and use 50% less energy – just the thing for a more sustainable planet.

### Sustainable light solutions

- Long lifetime up to 50,000 hours
- Ultra Efficient

### Premium quality

- Durable design with PowerShield coating

### Designed for outdoors

- IP65 weatherproof rated

### Special characteristics

- Motion sensor, for convenience and reassurance

### High-quality light

- High light output

# Highlights

## Long lifetime up to 50,000 hours



Reliable high-quality LED light lasts up to 50,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while enjoying the perfect garden light every night.

## Ultra Efficient



Consumes at least 50% less energy compared to equivalent standard LED lights from Philips.

## Durable design



Protected by PowerShield To keep your outdoor lights in excellent condition, we use a high-performance powder coating powered by Interpon, an AkzoNobel brand. Tougher than traditional paints, it protects against fading, scratches, dents and rust for long-lasting beauty and performance.

## IP65 weatherproof rated

An IP rating contains two digits which refer to protection against solids, such as dust, or liquids, such as rain. IP65 means that these light fixtures are protected against water splashed from any direction and are suitable for outdoor use.

## Motion sensor, for convenience and reassurance



A motion sensor is included to welcome you when you return home or let you know when someone's coming.

## High light output

Brighten up your home with high-quality light

# Specifications

## Design and finishing

- Colour: Anthracite
- Material: Metal

## Durability

- Nominal lifetime: 50,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

**Extra feature/accessory incl.**

- Adjustable spot head: Adjustable – rise and fall
- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: Yes
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: No
- Solar Energy: No
- Centrepiece: No

**Light characteristics**

- Colour rendering index (CRI): 80
- Colour temperature: 3000 K

**Miscellaneous**

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- LED innovations: UltraEfficient
- Extra Features: Water Resistant

**Power consumption**

- Power: 14

**Product dimensions and weight**

- Net weight: 0.404 kg
- Overall height: 190 mm
- Overall length: 160 mm
- Overall width: 60 mm

**Service**

- Warranty: 5 year(s)

**Technical specifications**

- Total lumen output fixture: 2600
- Bulb technology: LED
- Light colour: 3000
- Mains power: AC 220-240
- Fixture dimmable: No
- Energy class included light source: B
- IP code: IP65 | Dust-tight and jet-proof
- Class of protection: Class I – Earthed
- Light source replaceable: No
- Number of light sources: 1

**Packaging dimensions and weight**

- EAN/UPC - product: 8720169365384
- Net weight: 0.4 kg
- Gross weight: 0.46 kg
- Height: 19.7 cm
- Length: 6.7 cm
- Width: 16.6 cm



Issue date: 2026-03-21  
Version: 0.225

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)