

PHILIPS

Olas Fan Ceiling Light
28 (Fan) +24 (Light) W

Fan Ceiling Lights

3000/4300/6500K

Black

Remote Control

8720169369955



Dynamic light with a quiet, comfortable breeze

The Philips LED ceiling fan light combines dimmable, customisable white light with the comfort of a wide-blade ceiling fan for generous air flow. Easily create the perfect atmosphere in any space with SceneSwitch light settings and remote control.

Easy to experience

- Get year-round use

Ambient light effect

- Bright yet comfortable ceiling light

Control

- The remote control offers easy control of all the functions of the ceiling fan and light. Switch the light or fan on or off, choose from three fan speeds, cycle through SceneSwitch light settings, use the torch feature or set one of five timers.

Highlights

Get year-round use

With operation modes for both summer and winter, you'll get the best settings to circulate the air in your space all year round.

Bright yet comfortable ceiling light

The Philips LED ceiling fan light offers powerfully bright – yet comfortable – light for your home, which you can control with the included remote control or a wall switch.

Remote control included

The remote control offers easy control of all the functions of the ceiling fan and light. Switch the light or fan on or off, choose from three fan speeds, cycle through SceneSwitch light settings or timers.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Colour: Black
- Material: Metal

Durability

- Average life (at 2.7 hrs/day): 20 year(s)
- Number of switch cycles: 20,000
- Nominal lifetime: 20,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: Yes
- LED integrated: Yes
- Remote control included: Yes

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2700-4000-6500 K
- Warm-up time to 60% light: 2
- Luminous efficacy (rated) (nom.): 110

Miscellaneous

- Especially designed for: Bedroom, Dining Room, Living Room, Office
- Style: Contemporary
- Type: Fan Ceiling Lights
- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Remote control

Other characteristics

- Lamp current: 260 mA
- Fan Flow: 7,650 m³/h

Power consumption

- Power factor: 0.9

Product dimensions and weight

- Net weight: 4.2 kg
- Overall height: 310 mm

Service

- Warranty: 5 year(s)

Technical specifications

- Diameter: 1,060 mm
- Total lumen output fixture: 2650@4300K
- Bulb technology: LED
- Light colour: Tunable white light
- Mains power: AC 220-240
- Fixture dimmable: Yes
- IP code: IP20 | Finger-protected
- Class of protection: Class I – Earthed

What's supported

- Compatible operating systems: Not applicable

8720169369955

Packaging dimensions and weight

- EAN/UPC - product: 8720169369955
- Net weight: 4.2 kg
- Gross weight: 5.7 kg
- Height: 22.6 cm
- Length: 58.5 cm
- Width: 30.5 cm



Issue date: 2026-03-31
Version: 0.236

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com