

# PHILIPS

Valen Ceiling Light  
16W

Ceiling Lights

2200-6500 K

White

Dimmable; Remote Control;  
Tunable White; Warm Glow

8720169385139



## Set your desired ambience at your fingertips

With just a few simple clicks on the remote control, the Philips LED All-in-one ceiling light gives you the ultimate flexibility and convenience to personalise your light settings with ease. Comfortable light that's easy on your eyes. Create the desired ambience with lights that know your needs.

### High-quality light

- EyeComfort – light that's easy on your eyes

### Match your interior

- Super slim design

### Easy to experience

- Easy installation

### Control

- Enhance your moment. Tunable with dimming functions (remote control included)
- Adjustable colour temperature and brightness

# Highlights

## EyeComfort – light that's easy on your eyes



Poor-quality light can cause eye strain. With many people spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour

rendition and dimming effects to ensure that they meet EyeComfort requirements. This Philips LED luminaire not only delivers comfortable light, but also stays that way for the duration of its lifespan, delivering consistent light quality, output and colour for more than a decade.

### Super slim design

Slim design is ideal for low-ceiling rooms, sitting flush against the surface.

### Easy installation

No more hassle with installation. Just fix or hang securely on the wall or ceiling, and plug it in. Your new light fitting is now ready to light up your room!

## Enhance your moment. Tunable with dimming functions (remote control included)

Easy-to-use remote control lets you dim to the perfect light level for your mood.

## Adjustable colour temperature and brightness

Changing colour temperature and brightness allows you to change the mood and atmosphere in a room, matching the light to different kinds of activity.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

## Design and finishing

- Colour: White
- Material: Plastic

## Durability

- Average life (at 2.7 hrs/day): 20 year(s)
- Number of switch cycles: 20,000
- Nominal lifetime: 20,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Batteries included: No
- Dimmable with remote control: Yes
- LED integrated: Yes
- Remote control included: Yes

## Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2200–6500 K
- Warm-up time to 60% light: 2
- Luminous efficacy (rated) (nom.): 125

## Miscellaneous

- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Dimmable, Remote control, Tunable White, WarmGlow

## Other characteristics

- Lamp current: 140 mA

## Power consumption

- Power factor: 0.5

### Product dimensions and weight

- Net weight: 0.8 kg
- Overall height: 24 mm

### Service

- Warranty: 5 year(s)

### Technical specifications

- Diameter: 291 mm
- Total lumen output fixture: 2000 (@2700K)
- Bulb technology: LED
- Light colour: Tunable white light
- Mains power: AC 220-240
- IP code: IP20
- Class of protection: Class II – Double Insulated

### The bulb

- Software upgradable: No

### What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

### Packaging dimensions and weight

- EAN/UPC - product: 8720169385139
- Net weight: 0.8 kg
- Gross weight: 0.97 kg
- Height: 29.5 cm
- Length: 4.8 cm
- Width: 29.5 cm



Issue date: 2026-05-22  
Version: 0.286

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)