

PHILIPS

Filament Candle Clear
40W P45 E14 x3

LED

2700 K

470 lm

15000 h



8721103047304



Bright LED lighting

Philips LED light bulbs provide high-quality light, with a long life and immediate, significant energy savings.

Choose a simple replacement for your old lamps

- Similar shape and size as standard incandescent bulbs

Create the right light for your home

- A simple LED for everyday use

Highlights

Replaces standard incandescents



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional lustre
- Socket: E14
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

Lamp dimensions

- Height: 8 cm
- Width: 4.5 cm

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 300 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 470 lm

Miscellaneous

- EyeComfort: No

Other characteristics

- Efficacy: 109 lm/W

Packaging information

- EAN: 8721103047304
- EOC: 872110304730400
- Product title: LED classic 40W P45 E14 WW CL ND 3CT/8EC

Power consumption

- Power factor: 0.52
- Voltage: AC 220-240 V
- Wattage equivalent: 40 W
- Energy efficiency label (EEL): F
- Power Consumption: 4.3 W
- Energy consumption kWh/1,000 hours: 5

Product dimensions and weight

- Length: 8 cm

Technical specifications

- Frequency: 50-60 Hz
- EPREL Registration Number: 2136337

Packaging dimensions and weight

- EAN/UPC - product: 8721103047304
- Net weight: 0.04 kg
- Gross weight: 0.07 kg
- Height: 9.7 cm
- Length: 5.1 cm
- Width: 14.5 cm



Issue date: 2025-06-14
Version: 0.223

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com