

PHILIPS

Spot 35 W PAR16
GU10

Ultra Efficient

4000 K

215 lm

50000 h



8721103047588



A light bulb like no other

Philips LED spots provide a focused bright beam, an exceptionally long life and significant energy savings. This spot is the perfect long-lasting replacement for 35W spots with a GU10 cap.

Choose a simple replacement for your old lamps

- Similar shape and size to standard halogen bulb

Choose for a sustainable solution

- Long life bulb - Lasts up to 50 years

High-quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Similar shape and size to standard halogen lamp



With its beautifully shaped design and familiar dimensions, this is a modern lighting energy-saving, standard, LED bulb. The perfect sustainable replacement for traditional standard halogen bulbs.

Long life bulb - Lasts up to 50 years



With a lifetime of up to 50,000 hours, you can reduce the hassle of frequently replacing your light bulbs and enjoy a perfect lighting solution for over 50 years.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 50,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Beam angle: 36
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Nominal luminous flux: 215 lm
- Luminous efficacy (rated) (nom.): 179

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort, UltraEfficient

Packaging information

- EAN: 8721103047588
- EOC: 872110304758800
- Product title: LEDClassic 35W GU10 CW 36D ND UE SRT4

Power consumption

- Power factor: 0.25
- Voltage: AC 220-240 V
- Wattage: 1.2 W
- Wattage equivalent: 35 W
- Energy efficiency label (EEL): A
- Energy consumption kWh/1,000 hours: 2

Product dimensions and weight

- Overall height: 54 mm
- Overall length: 54 mm
- Overall width: 50 mm

Rated values

- Rated peak intensity: 390 cd

Technical specifications

- Frequency: 50-60
- Bulb technology: LED
- EPREL Registration Number: 2201337
- Can it be used in closed luminaires:
No

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8721103047588
- Net weight: 0.04 kg
- Gross weight: 0.11 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 6.3 cm



Issue date: 2026-05-13
Version: 0.102

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com