

PHILIPS

Valen Ceiling Light
17W Square

Ceiling Lights

2200-6500KK

Black

Dimmable; Remote Control;
Tunable White; Warm Glow

8721103060921



The right light for all your needs – at a touch

With Philips Valen remote-controlled ceiling luminaires, your lighting adapts to your life, not the other way around. With just a click, you can transform your space – whether you need energising brightness to focus or warm tones to relax. Exclusive dim-to-warm technology creates a cosy atmosphere of candlelight for that soft glow when you want to wind down. No complicated set-ups, no hassle – just seamless, intuitive control for every moment of your day. Remote control is included.

Create a warm atmosphere

- Dim-to-warm

Limitless possibilities

- Full flexibility to create the perfect ambience

Versatile lighting for every moment of your day

- Deep dimming to 1%

Easy to experience

- Easy to install

Control

- Easy to control

Highlights

Dim-to-warm

With WarmGlow technology, the light gets warmer in tone as it dims, just like a traditional incandescent bulb. Dim 2700 K as low as 2200 K and 1% to create a cosy, candlelight atmosphere.

Full flexibility to create the perfect ambience

Create the desired ambience for all of your spaces and activities by effortlessly choosing from five different settings: Nightlight (2700 K), Relax (2200 K), Bright(3000 K), Concentrate (4000 K) and Energise (6500 K)

Deep dimming to 1%

You can easily create the perfect ambience with deep dimming down to 1% – whether you want to watch film, dim the lights to get ready for bed or need a nightlight in the middle of the night.

Easy to install

A simple wiring connector and twist-and-lock mechanism means that luminaires can be installed quickly without the need for special tools or procedures. The remote control or wall switch are easily affixed to the wall, so they are always available when you want to turn the lights on or off.

Easy to control

Simply install Valen like a normal ceiling luminaire and start using it with the remote control or wall switch. No pairing, no mobile app – just unbox it, install it and control it using the remote control or wall switch. Select your preferred scenes or dimming levels with just a click. This light has a built-in memory chip which will memorise your last light setting, you can always keep your favourite scene.

Specifications

Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

Design and finishing

- Colour: Black
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 20 year(s)
- Number of switch cycles: 20,000
- Nominal lifetime: 20,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Batteries included: No
- Dimmable with remote control: Yes
- LED integrated: Yes
- Remote control included: Yes

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2200–6500 K
- Warm-up time to 60% light: 2
- Luminous efficacy (rated) (nom.): 120

Miscellaneous

- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Dimmable, Remote control, Tunable White, WarmGlow

Other characteristics

- Lamp current: 150 mA

Power consumption

- Power factor: 0.5

Product dimensions and weight

- Net weight: 1.9 kg
- Overall height: 40 mm
- Overall length: 400 mm
- Overall width: 400 mm

Service

- Warranty: 5 year(s)

Technical specifications

- Total lumen output fixture: 2050 (@2700K)
- Bulb technology: LED
- Light colour: Tunable white light
- Mains power: AC 220-240
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated

Packaging dimensions and weight

- EAN/UPC – product: 8721103060921
- Net weight: 1.6 kg
- Gross weight: 1.89 kg
- Height: 40 cm
- Length: 40 cm
- Width: 6.2 cm

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable



Issue date: 2026-04-15
Version: 0.496

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com