

PHILIPS

Bliss Fan Ceiling
Light

Fan Ceiling Lights

2700-6500K

Black

Dimmable; Remote Control;
Tunable White

8721103096043



Retractable-blade ceiling fan with dimmable and tunable LED light

The Philips Bliss retractable-blade ceiling fan with LED light will keep your indoor spaces bright, comfortable and stylish all day and all year. With an optimised aerodynamic fan blade design, powerful air volume and two airflow directions, our ceiling fan offers consistent performance, cooling quickly in the summer and circulating the air effectively in the winter. The whisper-quiet motor won't disturb your sleep or concentration, while the stable ceiling mount and perfectly weight-balanced fan blades minimise wobbling. The light itself offers the high light quality and adaptability that you've come to expect from Philips. Create the perfect ambience for every moment with smooth dimming (down to 5%) and tunable white light from warm white (3,000 K) to cool daylight (6,500 K). Our upgraded RF-based remote control lets you easily control your ceiling fan with LED light from anywhere within your home – no need to point the remote at the fan.

Easy setup

- Easy installation

Premium quality

- Quiet operation

Control

- Seamlessly adjustable ambience
- Intuitive remote control

Durability

- Powerful airflow
- Adjustable fan speed
- Two airflow directions

Highlights

Easy installation

The new mechanical design shortens the installation process from 16 steps to an easy 8; saving you time and effort

Quiet operation

Quiet DC motor (<50 dB – less than a refrigerator hum) won't disrupt your sleep or distract you when you need to concentrate; stable ceiling mount minimises wobbling

Seamlessly adjustable ambience

Philips ceiling fans with LED lights offer smooth dimming down to 5%, tunable white light ranging from warm white (3,000 K) to cool daylight (6,500 K), letting you create the perfect ambience for every moment

Intuitive remote control

With an intuitive RF-based remote control, you can easily control your ceiling fan with LED light from anywhere within your home – no need to point the remote at the fan

Powerful airflow

Our ceiling fan cools fast and effectively with a robust DC motor, optimised fan blade design with powerful airflow

Adjustable fan speed

The Philips ceiling fans let you choose from six fan speeds, allowing you to match the airflow exactly to your activities or the seasons

Two airflow directions

DC motor allows forwards and backwards airflow directions for year-round usage: cooling in the summer, warm air circulation in the winter

Specifications

Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

Design and finishing

- Colour: Black
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Number of switch cycles: 15,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: Yes

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2700-6500 K
- Warm-up time to 60% light: <2
- Luminous efficacy (rated) (nom.): 128

Miscellaneous

- Especially designed for: Bedroom, Living Room
- Style: Contemporary
- Type: Fan Ceiling Lights
- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Dimmable, Remote control, Tunable White

Other characteristics

- Lamp current: 310 mA
- Fan Flow: 7,980 m³/h
- Fan efficiency: 285

Product dimensions and weight

- Net weight: 6.2 kg
- Overall height: 29 mm

Service

- Warranty: 5 year(s)

Technical specifications

- Total lumen output fixture: 4500 @4000K
- Bulb technology: LED
- Light colour: Tunable white light
- Mains power: AC 220-240
- IP code: IP20 | Finger-protected
- Class of protection: Class I – Earthed

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8721103096043
- Net weight: 6.2 kg
- Gross weight: 9.86 kg
- Height: 29.1 cm
- Length: 55.9 cm
- Width: 55.9 cm



Issue date: 2026-04-15
Version: 0.240

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com